

Jul.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case that the application demands a high level of reliability, such as automotive,
 please contact a company representative for further information.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
APPLICABLE STANDARD										
RATING	VOLTAGE	250V AC			CURRENT	3A				
	OPERATING TEMPERATURE RANGE	-35 °C TO +85 °C(NOTE1)			STORAGE TEMPERATURE RANGE	-10°C TO +60 °C(NOTE3)				
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTE2)			STORAGE HUMIDITY RANGE	20% TO 70%(NOTE3)				
	APPLICABLE CONNECTOR	DF1B-*S-2.5R								
SPECIFICATIONS										
ITEM	TEST METHOD				REQUIREMENTS				QT	AT
CONSTRUCTION										
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.				×	×
MARKING	CONFIRMED VISUALLY.								×	×
ELECTRIC CHARACTERISTICS										
CONTACT RESISTANCE	100mA (DC OR 1000 Hz).				30mΩ MAX.				×	—
INSULATION RESISTANCE	500V DC.				1000MΩ MIN.				×	—
VOLTAGE PROOF	650V AC FOR 1 min.				NO FLASHOVER OR BREAKDOWN.				×	—
MECHANICAL CHARACTERISTICS										
CONTACT INSERTION AND EXTRACTION FORCES	□0.635±0.002 BY STEEL GAUGE.				INSERTION FORCE 4.4N MAX EXTRACTION FORCE 0.4N MIN				×	—
MECHANICAL OPERATION	50 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.				×	—
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, AT 2 h, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs.				×	—
SHOCK	490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.				② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.				×	—
ENVIRONMENTAL CHARACTERISTICS										
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 ~ 95 %, 96 h.				① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.				×	—
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55 →5 TO 35 →+85→5 TO35°C TIME 30 →10 TO 15 →30 →10 TO15min UNDER 5 CYCLES.				① CONTACT RESISTANCE: 30mΩ MAX. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.				×	—
REMARKS										
NOTE1:INCLUDING THE TEMPERATURE RISE BY CURRENT. NOTE2:NO CONDENSING. NOTE3:APPLY TO THE CONDITION OF LONG TERM STORAGE FOR UNUSED PRODUCTS BEFORE PCB ON BOARD, AFTER PCB BOARD, OPERATING TEMPERATURE AND HUMIDITY RANGE IS APPLIED FOR INTERIM STORAGE DURING TRANSPORTATION. Unless otherwise specified, refer to JIS C 5402					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
					<i>T. Kumogawa</i> '04.03.05	<i>T. Kumogawa</i> '04.03.05	<i>T. Miyajima</i> '04.03.08	<i>J. Ona</i> 04.03.09		
Note QT:Qualification Test AT:Assurance Test ×:Applicable Test										
HRS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET					
					PART NO. DF1B-*P-2.5DS(01)					
CODE NO.(OLD) CL			DRAWING NO. ELC4-162412-01			PART NO. CL541			1/1	

TO
 □
 □
 □

