

## DMO series - medium - Rubber hose



### Technical characteristics

**Technology:** Pipe locked with ratchet stop


**Max operating pressure:** 12 bar

**Construction:** Epoxy-coated steel case

**Connection:** 1 m of inlet supply hose

**Equipped with:** Fixed bracket

Fixed bracket  
 Inlet: G 3/8 F  
 Inlet: G 1/2 M for DMO 1315  
 + 1 m hose  
 Pressure: 12 bar  
 Temperature: -15°C to +40°C



A (mm)	B (mm)	C (mm)	ID/OD (mm)	Length (m)	Coupler	Flow rate (l/min)	Swivel inlet (BSPP)	Weight (kg)	Parts Numbers
485	475	237	8 x 14	10	BSI 06	500	G 3/8 F	16	<b>DMO 0810BS</b>
485	475	237	8 x 14	15	BSI 06	350	G 3/8 F	17.5	<b>DMO 0815BS</b>
485	475	237	8 x 14	20	BSI 06	260	G 3/8 F	19	<b>DMO 0820BS</b>
485	475	237	10 x 17	10	BSI 06	900	G 3/8 F	17	<b>DMO 1010BS</b>
485	475	237	10 x 17	15	BSI 06	700	G 3/8 F	19	<b>DMO 1015BS</b>
485	475	237	10 x 17	20	BSI 06	660	G 3/8 F	22	<b>DMO 1020BS</b>
485	475	237	8 x 14	10	ESI 07	500	G 3/8 F	16	<b>DMO 0810ES</b>
485	475	237	8 x 14	15	ESI 07	350	G 3/8 F	17.5	<b>DMO 0815ES</b>
485	475	237	8 x 14	20	ESI 07	260	G 3/8 F	19	<b>DMO 0820ES</b>
485	475	237	10 x 17	10	ESI 07	900	G 3/8 F	17	<b>DMO 1010ES</b>
485	475	237	10 x 17	15	ESI 07	700	G 3/8 F	19	<b>DMO 1015ES</b>
485	475	237	10 x 17	20	ESI 07	660	G 3/8 F	22	<b>DMO 1020ES</b>
485	475	237	13 x 20	15	ESI 07	1400	G 1/2 M	22	<b>DMO 1315ES</b>
485	475	237	8 x 14	10	ISI 06	500	G 3/8 F	16	<b>DMO 0810IS</b>
485	475	237	8 x 14	15	ISI 06	350	G 3/8 F	17.5	<b>DMO 0815IS</b>
485	475	237	8 x 14	20	ISI 06	260	G 3/8 F	19	<b>DMO 0820IS</b>
485	475	237	10 x 17	10	ISI 06	833	G 3/8 F	17	<b>DMO 1010IS</b>
485	475	237	10 x 17	15	ISI 06	700	G 3/8 F	19	<b>DMO 1015IS</b>
485	475	237	10 x 17	20	ISI 06	660	G 3/8 F	22	<b>DMO 1020IS</b>

A (mm)	B (mm)	C (mm)	ID/OD (mm)	Length (m)	Coupler	Flow rate (l/min)	Swivel inlet (BSPP)	Weight (kg)	Parts Numbers
485	475	237	13 x 20	15	ISI 08	1400	G 1/2 M	22	<b>DMO 1315IS</b>
485	475	237	8 x 14	10	CSI 06	500	G 3/8 F	16	<b>DMO 0810CS</b>
485	475	237	8 x 14	15	CSI 06	350	G 3/8 F	17.5	<b>DMO 0815CS</b>
485	475	237	8 x 14	20	CSI 06	260	G 3/8 F	19	<b>DMO 0820CS</b>
485	475	237	10 X 17	10	CSI 06	833	G 3/8 F	17	<b>DMO 1010CS</b>
485	475	237	10 x 17	15	CSI 06	700	G 3/8 F	19	<b>DMO 1015CS</b>
485	475	237	10 x 17	20	CSI 06	660	G 3/8 F	22	<b>DMO 1020CS</b>
485	475	237	13 x 20	15	CSI 08	1400	G 1/2 M	22	<b>DMO 1315CS</b>