



Main

Range	Linergy
Range of product	Linergy
Product or component type	Copper busbar
Product name	Linergy BS
Range compatibility	Prisma P enclosure
Busbar description	Flat bar
Quantity per set	Set of 1

Complementary

Installation direction	Vertical, operating position: rear Vertical, operating position: lateral
Installation description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm
[I _e] rated operational current	1400 A at 35 °C
[I _{cw}] rated short-time withstand current	25 KA (1 s) for 3 supports 50 KA (1 s) for 5 supports 65 KA (1 s) for 7 supports 75 KA (1 s) for 9 supports
Permissible current	1400 A at 35 °C: ≤ IP31 1250 A at 35 °C: > IP31
Busbar cross section	60 x 10 mm
Length	1675 mm
Height	1840 mm
Width	140 mm
Depth	20 mm
Net weight	8.24 kg
Type of busbar connection	Ø 10 mm drilled hole
Connection pitch	Connection each 25 mm
Support thickness	10 mm

Environment

Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	8.24 kg
Package 1 Height	2 cm
Package 1 width	14 cm
Package 1 Length	184 cm
Unit Type of Package 2	P2M
Number of Units in Package 2	80

Package 2 Weight	659.2 kg
Package 2 Height	35 cm
Package 2 width	120 cm
Package 2 Length	200 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
PVC free	Yes
Halogen content performance	Halogen free plastic parts product