

Han K 6/12 Pos. M Insert (6-10mm²)




Image is for illustration purposes only. Please refer to product description.

Part number	09 38 018 2602
Specification	Han K 6/12 Pos. M Insert (6-10mm ²)
HARTING eCatalogue	https://harting.com/09380182602

Identification

Category	Inserts
Series	Han-Com [®]
Identification	Han [®] K 6/12

Version

Termination method	Axial screw termination / screw termination
Gender	Male
Size	16 B
Number of contacts	18
Number of signal contacts	12
Number of power contacts	6
PE contact	Yes

Technical characteristics

Conductor cross-section	6 ... 10 mm ² Power 0.2 ... 2.5 mm ² Signal
Wire outer diameter	≤6.1 mm
Rated current	40 A
Rated voltage	690 V
Rated impulse voltage	8 kV
Pollution degree	3
Rated current (signal)	10 A
Rated voltage conductor-earth (signal)	230 V



Pushing Performance
Since 1945

Technical characteristics

Rated voltage conductor-conductor (signal)	400 V
Rated impulse voltage (signal)	4 kV
Pollution degree (signal)	3
Rated current acc. to UL	40 A
Rated voltage acc. to UL	600 V
Rated current acc. to UL (signal)	10 A
Rated voltage acc. to UL (signal)	600 V
Rated current acc. to CSA	40 A
Rated voltage acc. to CSA	300 V
Rated current acc. to CSA (signal)	10 A
Rated voltage acc. to CSA (signal)	300 V
Insulation resistance	$>10^{10} \Omega$
Contact resistance	$\leq 0.5 \text{ m}\Omega$
Contact resistance, signal area	$\leq 3 \text{ m}\Omega$
Stripping length	8 ... 9 mm 7.5 mm Signal
Tightening torque	2 Nm Contact screw M3 0.5 Nm Signal 2 Nm PE screw M5
Recommended screw driver	Slotted 0.5 x 3 Slotted 0.6 x 3.5 Slotted 0.8 x 4.5 PH2
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	145.7 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140056442
eCl@ss	27440205 Contact insert for industrial connectors
ETIM	EC000438
UNSPSC 24.0	39121522