

Grass Shear LXT®

DUM604

18V • 2 500 min⁻¹ • 160 mm

For grass trimming and cutting

A handy and light tool for grass trimming and cutting. Includes blades for grass trimming.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Cutting width	160 / 200 mm
Cutting height positions	3
Mowing Height	15 - 25 mm
Sound Pressure Level (L _{pA})	73 dB(A)
Sound Power Level (L _{WA})	82 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,8 kg
Product Dimensions (L x W x H):	353 x 177 x 131 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Strokes per Minute (SPM)	2500 min ⁻¹
Product net weight	1,1 kg
Vibration Level (3 axes)	≤ 2,5 m/s ²

User benefits

- Electronic overload protection protects the user and the device
- Ergonomically designed handle with sure grip provides more control and comfort
- Various cutting heights to cut the lawn
- Tool-less blade changing system enables simple and easy blade changes
- Dual blade action cuts quickly with a shearing effect
- Compact and lightweight design
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

195267-4

Shear blade assembly set 160 mm,



452055-5

Blade cover 200 mm



E-05658

Ultimate Knee Pad Set



Other

User manual

Parts drawing