

Lexium 62 Single Drive 15 A - accessory kit included

LXM62DD15C21000

EAN Code: 3606485317724

Main

Range of product	PacDrive 3
Device short name	LXM 62
Product or component type	Single drive
Component name	LXM62

Complementary

Product compatibility	Servo motor SHS Servo motor SH3 (70 mm, 2 motor stacks)optimized in terms of torque and speed Servo motor SH3 (70 mm, 3 motor stacks)optimized in terms of torque and speed Servo motor SH3 (100 mm, 1 motor stacks)optimized in terms of torque and speed Servo motor SH3 (100 mm, 2 motor stacks)optimized in terms of torque and speed Servo motor SH3 (100 mm, 2 motor stacks)optimized in terms of high torque Servo motor SH3 (100 mm, 3 motor stacks)optimized in terms of high torque Servo motor SH3 (140 mm, 1 motor stacks)optimized in terms of high torque Servo motor MH3 (70 mm, 2 motor stacks)optimized in terms of torque and speed Servo motor MH3 (70 mm, 3 motor stacks)optimized in terms of torque and speed Servo motor MH3 (100 mm, 1 motor stacks)optimized in terms of torque and speed	
Network number of phases	Three phase	
[Us] rated supply voltage	400 V (- 1010 %) for three phase 230 V (- 1010 %) for three phase 230 V (- 1010 %) for single phase	
Supply frequency	50/60 Hz - 55 %	
Continuous output current	5 A at 4 kHz	
Output current 3s peak	15 A at 4 kHz	
Continuous power	2.4 kW	
Nominal power	2.4 kW	
Switching frequency	8 kHz	
Overvoltage category	III	
Electrical connection	Terminal, clamping capacity: 0.215 mm², AWG 24AWG 16 (CN4) Terminal, clamping capacity: 0.516 mm², AWG 20AWG 6 (CN5) Terminal, clamping capacity: 0.7516 mm², AWG 18AWG 6 (CN6) Terminal, clamping capacity: 0.26 mm², AWG 24AWG 10 (CN7)	
Tightening torque	CN1: 2.5 N.m	
Number of inputs	2 digital 2 touch probe	
Discrete input voltage	24 V DC for - 2025 %	
Number of outputs	2 digital	
Discrete output voltage	24 V DC	
Safety function	STO (safe torque off)	

Communication interface	SERCOS III, integrated	
Depth	270 mm	
Height	310 mm	
Width	44.5 mm	
Net weight	3 kg	

Environment

Standards	CSA C22.2 No 14	
	IEC 61800-5-1	
	ISO 13849-1	
	ISO 13849-2	
	UL 508C	
	IEC 61508	
	IEC 62061	
	IEC 61800-5-2	
	IEC 61800-3	
Product certifications	CSA	
	TÜV	
	CE	
	EAC	
	UL	
IP degree of protection	IP20 conforming to IEC 60529	
Vibration resistance	10 m/s² conforming to IEC 60721-3-3	
Shock resistance	100 m/s² conforming to IEC 60721-3-3	
Pollution degree	2 conforming to IEC 61800-5-2	
Environmental characteristic	3K3 conforming to IEC 60721-3-3	
Relative humidity	585 %	
Ambient air temperature for operation	555 °C	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	34.000 cm
Package 1 Length	44.000 cm
Package 1 Weight	3.856 kg
Unit Type of Package 2	S06
Number of Units in Package 2	10
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	51.560 kg

Logistical informations

Country of origin

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∅ Environmental footprint

Environmental Disclosure

Product Environmental Profile

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	60beca05-ce1c-43ef-b5f4-b7c0f3eb7d27
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No