


FEATURES

- **High chemical resistance:** Ensures longevity and reliability in harsh chemical environments
- **Wide temperature range:** Operates effectively from -20 °C to 140 °C, suitable for various applications
- **Durable material:** Constructed from Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton for enhanced durability
- **Precision dimensions:** Inside diameter of 18.72 mm and thickness of 2.62 mm for accurate fitting
- **Compliance with standards:** Meets BS ISO 3601-1, AS 568, and other key standards for quality assurance

RS PRO 18.72 mm O-Ring Seal, Shore A 90 to 95

RS Stock No: 732-031



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO O-Ring Seal is designed for reliable sealing in various industrial applications. Made from high-quality materials such as Fluorinated Ethylene Propylene, Fluoroelastomer, and Viton, it offers excellent resistance to chemicals and extreme temperatures. With an inside diameter of 18.72 mm, it is ideal for use in demanding environments where durability and performance are critical.

General Specifications

Colour	Black
Hardness	Shore A 90 to 95
Product Type	O-Ring Seal
Sub Type	O-Ring

Mechanical Specifications

Inside Diameter	18.72 mm
Material	Fluorinated Ethylene Propylene, Fluoroelastomer, Viton
Outside Diameter	23.96 mm
Thickness	2.62 mm

Operation Environment Specifications

Maximum Operating Temperature	140 °C
Minimum Operating Temperature	-20 °C

Approvals

Standards/Approvals	BS ISO 3601-1, AS 568, EC 1935:2004, FDA, ISO 14001:2015, ISO 45001:2015, ISO 9001:2015, LABS, TSCA, USP Class VI, WRAS
---------------------	---

