

Order Code: TBS009



30,000
Hours



3 Years
Warranty



Performance Data

Input Power (W)	9
Lumens (lm)	800
System Efficacy (Lumens/Watt)	90
Rated Life (Hours)	30000
Colour Temperature (K)	6500
Colour Rendering (Ra)	80
Beam Angle (°)	160°

Electrical Data


Input Voltage (V) $\pm 10\%$	220-240
------------------------------	---------

Safety Thermal

Maximum Ambient Temperature (°C)	+40
Minimum Ambient Temperature (°C)	-20

Physical Data

Lens Type	Thermal Plastic
Case Material	Aluminium Substrate
Dimensions (mm)	600mm (T8) G13
Weight (kg)	0.05kg
IP Rating	IP20



Notes:

This Product Specification contains data about typical performance at nominal power. Actual values may depend on ballast and applications. Complies with (CE), Low Voltage (CE), WEEE and RoHSDirective.

Data is based upon tests performed by Venture Lighting in a controlled environment and is representative of relative performance at the relevant nominal power/voltage (e.g. 110/240/415). Actual performance can vary depending on operating conditions.

Data is subject to change without notice.