




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **5**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-0**

Features

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	5
---------------------	---

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

--



Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	7.11 mm[.28 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on




requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 63933-2 250 PL MKIII REC. 22-18AWG TPBR	 TE Part # 63854-2 250 PL MKIII REC. 18-14AWG TPBR	 TE Part # 1969383-2 FF 187&250 TAB HSG 9P NYLON NAT	 TE Part # 1217092-2 PL 250 TERMINAL REC 16-12 AWG TPBR
 TE Part # 63933-1 PL .250 TERMINAL REC 22-18 AWG BR	 TE Part # 1217092-1 PL 250 TERMINAL RECEPTACLE 16-12 AWG BR	 TE Part # 63854-1 250 PL MKIII REC. 18-14AWG BR	

Also in the Series | Mark III

 Crimp Terminal Housings(177)	 Quick Disconnects(173)
---	--

Also in the Series | Positive Lock 250

 Automotive Terminals(1)	 Crimp Terminal Housings(177)	 Insertion & Extraction Tools(3)	 Insulation Boots & Sleeves(5)
--	--	--	--



[Quick Disconnects\(173\)](#)


Customers Also Bought



TE Part #63896-1
[250 FASTON REC 16-12 AWG BR](#)



TE Part #63854-2
[250 PL MKIII REC. 18-14AWG TPBR](#)



TE Part #2-520263-2
[ULTRA-FAST 250 ASY REC 22-18 TPBR](#)



TE Part #41274
[250 FASTON,REC.,18-14 AWG,TPBR](#)



TE Part #41772
[250 FASTON REC 22-18 AWG TPBR](#)



TE Part #1742539-3
[CLUSTER BLOCK RECEPT,TPCuFeP](#)




TE Part #42111-3
[RING TONGUE TERMINAL 18-14 AWG TPBR](#)



TE Part #521367-2
[ULTRA-POD 250 ASSY REC 18-14 AWG TPBR](#)



TE Part #60394-1
[RING TERMINAL 20-16 AWG BR](#)



TE Part #S1033ET22P1
[TEMPERATURE SENSOR ASSEMBLY](#)

Documents

Product Drawings

[250 HSG. PL MKIII REC. 7.11mm 5P NAT](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_521780-1_C.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_521780-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_521780-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Positive Lock Receptacles](#)

English

[Positive Lock HVAC Motor Connectors](#)

English

Agency Approvals

[UL Report](#)

English