


AC2398



AS-Interface illuminated pushbutton module

AS-i Module 2BI 2LO RD/GR



Application	
Application	field installation
Electrical data	
Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	55
Inputs	
Sensor supply of the inputs	AS-i
Operating conditions	
Ambient temperature [°C]	-25...60
Storage temperature [°C]	-40...85
Protection	IP 67
Tests / approvals	
EMC	EN 61000-6-2 EN 62026-2
AS-i classification	
AS-i version	2.11; 3.0
Extended addressing mode	yes
AS-i master profile	M2; M3; M4
AS-i profile	S-B.A.E

AC2398



AS-Interface illuminated pushbutton module

AS-i Module 2BI 2LO RD/GR

AS-i I/O configuration	[hex]	B			
AS-i ID code	[hex]	A.E			
AS-i certificate		134701			
Assignment of the data bits	data bit	D0	D1	D2	D3
	LED	1	2	-	-
	pushbutton	-	-	1	2

Mechanical data

Weight	[g]	131.6			
Housing		housing for DIN rail mounting			
Type of mounting		mounting on DIN rail			
Dimensions	[mm]	100 x 46 x 45			
Materials		PA			

Displays / operating elements

Display	operation	LED, green
	errors	LED, red
Operating elements	2	freely programmable backlit function keys


Electrical connection

Module connection	M12
-------------------	-----

Remarks

Remarks	The pushbuttons (EAO type 84) provide protection against accidental contact. Housing and pushbuttons can be labelled.
Pack quantity	1 pcs.

Electrical connection



1	AS-i +
3	AS-i -