



DCS391NT

18V XR Li-Ion Circular Saw - Bare Unit

Selling Proposition

- Extremely durable tool design, including a cast magnesium base for repetitive, accurate cuts
- Keyless bevel angle and depth of cut adjustment with easy to read scale for maximum cordless versatility
- Spindle lock for quick and easy blade change
- Lock off switch and electronic motor brake for additional control and work safety
- Ultra thin kerf 165 mm, 24 tooth carbide-tipped blade allows for efficient run time and fast, smooth cut finish at maximum 55 mm depth of cut
- Includes heavy-duty TSTAK VI kitbox

Standard Equipment

- 165 mm carbide blade
- Hex Key
- Dust Port
- Battery and charger sold separately
- TSTAK VI heavy-duty kitbox

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Output	460 Watt
No Load Speed	3700 rpm
Blade Diameter	165mm
Blade Bore	20mm
Bevel Capacity	50°