



Fuse-link, medium voltage, 6.3 A, AC 17.5 kV, 2", 51 x 292 mm, back-up, DIN, with striker

17.5TDLSJ6.3

General specifications

Product name	Eaton Bussmann series medium voltage DIN fuse
Part no.	17.5TDLSJ6.3
EAN	5027590438216
Product Length/Depth	292 millimetre
Product height	51 millimetre
Product width	51 millimetre
Product weight	1700 gram
Compliances	IEC 60282-1 VDE 0670-4 DIN 43625
Product Tradename	None
Product Type	Medium voltage DIN fuse
Product Sub Type	None

Electrical data

Amperage Rating	6.3 A
Voltage rating	17.5 kV
Breaking capacity	35.5 kA
Performance Cat According To IEC 60282-1	Back-up
Rated frequency - min	50 Hz
Class	Class back-up
Resistance	313 Ohms

Product specifications

Application	indoor or outdoor use transformer protection
Fuse indicator	With Striker
Fuse size	51 x 292 mm
Standard	DIN
Mounting method	Clip-in

Compatible fuse clip

Used with	A3354710 Fuse clip 270303 Fuse clip
-----------	--

Technical data ETIM 9.0

Circuit breakers and fuses (EG000020) / Medium/high voltage fuse (EC003507)		
Electric engineering, automation, process control engineering / Electrical installation, device / Miniature circuit breaker system (MCB) / Medium-/high voltage fuse (ecl@ss13-27-14-19-11 [AGA534005])		
Rated current	A	6.3
Rated voltage	kV	17.5
Voltage type		AC
Rated frequency	Hz	50 - 50
Breaking capacity	kA	35.5
Utilization category		Other
Application		Primary side transformer protection
Length	mm	292
Diameter	mm	51
Performance category according to IEC 60282-1		Back-up
With striker		Yes
Standard		DIN

Release characteristic		Other
Installation technique		Air