



M12 Connectivity

M12, 4 pole, 90°, female connector to open ended lead **Stock No's 174-7857, 174-7858**



Primary Features

Knurled and hexagonal combination nut ensures secure connection

Integrated corrugated conduit locking system


IP65, IP67 when inserted and tightened

UL and CSA approved

Available in lengths: 2 Meters (RS 174-7857) 5 Metres (RS 174-7858)







 1 ~	ı brown (+)
2 >	white (N/C)
4 >	black (N/O)
_	
3 >	blue (–)
	 - -

Female







Cable	174-7857, 174-7858
No./diameter of wires	4 × 0.34 mm ²
Wire isolation	PVC (br, wh, bl, bk)
Material (jacket)	PVC (UL/CSA)
Outer Ø	5.0 mm ±5%
Bend radius (moving)	10 × outer Ø
Temperature range (fixed)	-30+80 °C
Temperature range (mobile)	-5+80 °C
Cable identification	614
Cable type	1 (PVC)
Approval (cable)	UL (AWM-Style 2464/1731), CSA
Cable weight [g/m]	40,70
Material (wire)	Cu wire, bare
Resistor (core)	max. 60 Ohm/km (20 ° C)
Single wire Ø (core)	0.15 mm
Construction (core)	19 × 0.15 mm (multi-strand wire class 5)
Diameter (core)	4 × 0.34 mm²
AWG	similar to AWG 22
Material (wire isolation)	PVC
Material property (wire isolation)	CFC-, cadmium-, silicone- and lead-free
Shore hardness (wire isolation)	45 ±5 D
Wire-Ø incl. isolation	1.25 mm ±5%
Color/numbering of wires	br, bk, bl, wh
Stranding combination	4 wires twisted
Shield	no
Material (jacket)	PVC
Material property (jacket)	CFC-, cadmium-, silicone- and lead-free
Shore hardness (jacket)	85 ±5 A
Outer-Ø (jacket)	5.0 mm ±5%
Color (jacket)	black
chemical resistance	good resistance to oil, gasoline and chemicals
Nominal voltage	UL 300 V AC





Cable continued	174-7857, 174-7858
Testvoltage	2000 V AC
Current load capacity	to DIN VDE 0298-4
Temperature range (fixed)	-30+80 °C
Temperature range (mobile)	-5+80 °C
Bend radius (fixed)	5 × outer Ø
Bend radius (moving)	10 × outer Ø
Jacket Color	black
Technical Data	
Operating voltage	max. 250 V AC/DC
Operating voltage (only UL listed)	max. 30 V AC/DC
Operating current per contact	max. 4 A
Rated surge voltage	2.5 kV
Material group	IEC 60664-1, category I
Coding	A-coded
Locking of ports	Screw thread M12 \times 1 mm (recommended torque 0.6 Nm) self-securing
Compression gland	M12 (SW13)
Protection	IP65, IP66K, IP67 inserted and tightened (EN 60529)
Locking material	Zinc die casting, matte nickel plated
Material	PUR
suitable for corrugated tube (internal Ø)	10 mm
Standards	DIN EN 61076-2-101 (M12)
Pollution Degree	3
Temperature range	-25+85 °C, depending on cable quality