

Description

STAINLESS STEEL BOLT HOLE CASTOR, BLUE ELASTIC RUBBER 80MM

Fixed


Part Number
Swivel
KP410A080-571L



Swivel and brake
KP410D080-571L



	Fixed	Swivel	Swivel+brake
Wheel Diameter ØD	80 mm		
Overall Height H	108 mm ±1		
Center hole	13 mm		
Offset F ±1	\	42 mm	42 mm
Width of Tread	34 mm±0,5		
Hardness of tread	shore A ± 70°		
Load capacity	100 Kg		
Weight		0,6 kg	0,71 kg
Temperature	- 20 / + 60 °C		



Castor Assembly :

Pressed stainless steel -AISI 304-. Swivel on two rows of balls.
Central bolt hole fitting
Total lock. Metal pedal.

Wheel :

Wheel centre made of Black Polyamide.
Tread : Solid, Blue bonded elastic Rubber. Non marking.
Hub : Plain bore.

Features :

Low starting effort. High load capacity.
Smooth and quiet handling on all types of floors.
Absorbs shocks and vibrations. Resistant to wear.
100% anti-corrosion. Easy to clean. Specially designed for humid environments.
Suited for Food industry, Hospital or Industrial Kitchen equipment.
Non staining blue rubber.
Medium duty.