

Switch Mode Power Supply

ATX12V v.2.2 & EPS12V v2.91~ 12cm fanActive PFC



Dimension: W150 x L140 x H86mm
(5.9" x 5.5" x 3.4")



Features

Specification compliance: ATX12V v2.2 & EPS12V v2.91
Support the latest Intel & AMD Socket
PCI Express & Serial ATA ready
Double forward converter circuit
High efficiency and reliability
Low ripple & noise
Super low noise fan control
Short circuit protection on all outputs
Over voltage protection
Over power protection
100% hi-pot test
100% burn in, high temperature cycled on/off

AC input voltage & DC output

Model	DC output								Input voltage	
	+3.3V	+5V	+12V1	+12V2	+12V3	+12V4	-12V	+5Vsb	Total power	Full range Fixed 220V
SS-650HT Active PFC	24A	30A	18A	18A	18A	18A	0.8A	3A	650W	Yes ---
	170W Max. ¹		52A ²				9.6W	15W		
SS-550HT Active PFC	24A	30A	18A	18A	18A	18A	0.8A	3A	550W	Yes ---
	170W Max. ¹		41A ²				9.6W	15W		

Remarks: 1. Combined +3.3VDC & +5V DC maximum power

specification may change without prior notice

Electrical Specification

Input frequency: 47/63Hz
In-rush current, cold start: 100A max.
Hold up time, full load: 12ms. typical
Efficiency: at normal input voltage ≥80%
Line regulation: '+/- 1% typical
Load regulation: '+/- 5% typical
Cross regulation: '+/- 5% typical
Ripple / noise: 1%
Standby mode <5W
MTBF, full load @ 25°C amb. Excluding the DC fan: >100k hrs
Power Factor Correction: Active PFC 99% typical

Sea Sonic Electronics Co., Ltd. Head Office:

8F, #19, Alley 360, Sec. 1, Neihu Road,
Neihu, Taipei, Taiwan, R.O.C.

Tel: +886 2 2659 0338
Fax: +886 2 2659 0530
sales@seasonic.com.tw
www.seasonic.com

Factories:

I. Tao Yuan, Taiwan.
II. Dong Guan, China.

USA office:

Tel: +1 626 969 9966
Fax: +1 626 969 9986
usa@seasonic.com

Safety compliance

CUL, TUV, CB, CCC, D, N, S, FI, GOST-R, BSMI

EMI/RFI compliance

CE, FCC, C-tick

ISO 14001



REGISTERED FIRM



REGISTERED FIRM