

400 10X11

Double ended ring spanner

open

Code
6057270

ETIM
EC002188

EAN
4010886605721

UNSPSC
27-11-17-05

Country of origin
Germany

eCl@ss
21-04-01-06

Customs tariff number
82041100



Article description

- Acc. to DIN 3118
- Sizes 8x10 to 12x14 mm with hexagon
- Vanadium steel 31CrV3, chrome-plated
- Application on hydraulic/brake lines
- Use:
- Heads 15° angled
- Hexagonal opening 30° offset, UD profile opening 15° offset

Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	22 mm
Version/Execution	Heads 15° angled hexagonal Opening 30° offset, UD profile Opening 15° offset	Head height 2 [mm]	8,5 mm
Net weight [kg]	0,064 kg	Head height 1 [mm]	8 mm
Total length [mm]	150 mm	Width of head 1 [mm]	20,0 mm
Total width [mm]	22 mm	Width across flats [mm]	10x11
Total height [mm]	12 mm	Width across flats 2 [mm]	11
Surface	chrome-plated	Ring profile	hexagonal
Use	Application on hydraulic/brake lines	Opening width 1 (min.) [mm]	7,0 mm
Material	31CrV3	Opening width 2 (max.) [mm]	8,5 mm
Standard	DIN 3118	Weight	0,140 lbs
Width across flats 1 [mm]	10	Ring angle	15°