

## Industrial Ethernet IE-SW-BL08-8TX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

### Product image



- Variations with 5 or 8 ports
- Variations for Gigabit Ethernet
- Sturdy metal housing
- Compact design
- Two redundant power inputs 12/24/48 V DC
- Variations with copper and fibre-optic interface (multimode and singlemode)
- Extensive approvals: CE, FCC, cULus, Class I Div. 2 / ATEX Zone 2, DNV-GL

### General ordering data

Type	IE-SW-BL08-8TX
Order No.	<a href="#">1240900000</a>
Version	Network switch, unmanaged, Fast Ethernet, Number of ports: 8x RJ45, IP30, -10 °C...60 °C
GTIN (EAN)	4050118028911
Qty.	1 pc(s).

Creation date September 30, 2020 10:42:45 AM CEST

Catalogue status 25.09.2020 / We reserve the right to make technical changes.

**Industrial Ethernet  
IE-SW-BL08-8TX**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**
**Dimensions and weights**

Width	50 mm	Width (inches)	1.969 inch
Height	114 mm	Height (inches)	4.488 inch
Depth	70 mm	Depth (inches)	2.756 inch
Net weight	275 g		

**Environmental Product Compliance**

REACH SVHC Lead 7439-92-1

**EMC conformity and approvals**

EMC standards	EN 55032, EN 55024, CISPR 32, FCC Part 15 Subpart B Class A, IEC 61000-4-2 ESD: Contact: 6 kV; Air: 8 kV, IEC 61000-4-3 RS: 80 MHz to 1 Ghz: 10 V/m, IEC 61000-4-4 EFT: Power: 2 kV; Signal: 1 kV, IEC 61000-4-5 Surge: Power: 2 kV; Signal: 2 kV, IEC 61000-4-6 CS: 10 V, IEC 61000-4-8	Safety standard	UL508
Explosive risk zone	UL/cUL, Class I, Division 2, Groups A, B, C and D, ATEX Zone 2 Ex nA IIC T4 Gc	Ship use	DNV-GL
Shock	according to IEC 60068-2-27	Vibration	according to IEC 60068-2-6
Free fall	According to IEC 60068-2-32		

**Environmental conditions**

Humidity	5 to 95 % (non-condensing)	Operating temperature, max.	60 °C
Operating temperature, min.	-10 °C	Storage temperature, max.	85 °C
Storage temperature, min.	-40 °C		

**Guarantee**

Time interval 5 years

**Interfaces**

DIP switch	1x for enabling/disabling the broadcast storm protection	LED indicator	PWR1, PWR2, 10/100M (TP-Port)
Number of ports	8x RJ45	RJ45 ports	10/100BaseT(X), auto negotiation, Full-/half-duplex mode, Auto MDI/MDI-X port

**MTBF**

MTBF 2,701,531 hrs Database Telcordia (Bellcore), GB

Creation date September 30, 2020 10:42:45 AM CEST

## Industrial Ethernet IE-SW-BL08-8TX

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technical data

### Power supply

Connection type	1 removable 4-pin terminal block		
Voltage supply	12/24/48 V DC, 2 redundant inputs		
Voltage supply range	Voltage type	DC	
	Voltage, min.	9.6 V	
	Voltage, max.	60 V	
Current consumption	0.13 A at 24 V		
Reverse polarity protection	Available		
Overload current protection	1.1 A		

### Switch characteristics

Bandwidth backplane	1.6 Gbps	MAC table size	2 K
Packet buffer size	768 Kbit		

### Technical data

Housing main material	Aluminium	Protection degree	IP30
Type of mounting	DIN rail, Panel (with optional mounting kit)		

### Technology

Data switching	Store and Forward	Flow control	IEEE 802.3x flow control, Back pressure flow control
Standard	IEEE 802.3 for 10BaseT, IEEE 802.3u for 100BaseT(X), IEEE 802.3x for flow control		

### Classifications

ETIM 6.0	EC000734	ETIM 7.0	EC000734
eClass 9.0	19-17-01-06	eClass 9.1	19-17-01-06
eClass 10.0	19-17-04-02		

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">DNV-GL certificate</a> <a href="#">ATEX certificate</a> <a href="#">KC certificate</a> <a href="#">EU Declaration of Conformity</a>
Engineering Data	<a href="#">EPLAN, WSCAD, Zuken E3.S</a>
Engineering Data	<a href="#">STEP</a>
Product Change Notification	<a href="#">Product Change Notification IE-SW-BL08-series</a>
User Documentation	<a href="#">Hardware Installation Guide</a>

Creation date September 30, 2020 10:42:45 AM CEST