

Parker Product Datasheet



Manually-operated valves offer a reliable and durable system for opening and closing the circuit when the system has to be switched frequently.

They provide a significant reduction in the time needed to work on pneumatic circuits.

PART NUMBER: 7800 04 19
CONNECTION 1 THREAD STYLE: Metric
SHAPE: 3/2 manual switch-operated valve supply
HANDLE: NICKEL PLATED BRASS
GRIPPING RING: STAINLESS STEEL
BODY MATERIAL: TECHNICAL POLYMER
CONNECTION 2 TUBE O.D. (MM): 4
CONNECTION 1 THREAD SIZE (METRIC): M5x0,8

PRODUCT OVERVIEW

Manually-operated valves offer a reliable and durable system for opening and closing the circuit when the system has to be switched frequently.

They provide a significant reduction in the time needed to work on pneumatic circuits.

Features/Benefits:

- Manual Switch-Operated Valves

- Downstream control supply provided by simply moving the lever
- 2 models available to provide the best solution for the system:
3/2: opening, closing, venting

2/2: opening, closing

- Compact and ergonomic (can be positioned through 360°)
- Push-in connections

- Valves with Sliding Sleeve

- Uni-directional use ensures the downstream circuit is vented
- Operated in the plane of the tube
- Lightweight due to the use of aluminium
- Ideal for complex installations in a restricted space
- Immediate identification of the venting system by the colour (red)

Product Types:

- 3/2 Manual Switch-Operated Valve, Supply, Male BSPP and Metric Thread
- 3/2 Manual Switch-Operated Valve, Control, Male BSPP Thread
- 2/2 Manual Switch-Operated Valve, Male BSPP Thread
- 3/2 Sleeve Valve, Female BSPP and Metric Thread

Markets:

- Factory Automation
- Wearing Apparel
- Semiconductor
- Packaging

Application:

- Pneumatic Circuits Repeated Venting

Technical Characteristics:

- Fluids: Compressed air
- Materials: nickel-plated brass, technical polymer, NBR, silicone free

• Pressure: 0 to 10 bar

Model 0669: 0 to 16 bar

- Temperature: -10°C to +80°C

Model 0669: -5°C to +70°C

Regulations:

- DI: 2002/95/EC (RoHS)
- RG: 1907/2006 (REACH)
- DI: 97/23/EC (PED)

Technologies:

- Sleeve valve
- Pneumatic systems
- Pressure regulating valve
- Function fitting

TECH SPECIFICATIONS

MINIMUM OPERATING TEMPERATURE	-10 °C
MEDIA	Compressed air
MAXIMUM OPERATING TEMPERATURE	80 °C
MAXIMUM OPERATING PRESSURE	10 barg
WEIGHT	0.032 kg
DIVISION	Low Pressure Connectors Europe Division
SPECIFICATIONS MET	DI: 2002/95/EC (RoHS), RG: 1907/2006 (REACH), DI: 97/23/EC (PED)
VACUUM PRESSURE RATING	755 mm-Hg
O-RING MATERIAL	NBR
QUANTITY PER BOX	2
APPLICATION	Robotics, Conveyors, Textile, Plastics Engineering, Printing, Pneumatics, Packaging