




SFP56

TE Internal #: 2349201-6
zSFP+ Stacked (SFP56), Cage Assembly with Integrated Connector,
.6mm [.018in] Centerline, Signal

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP56 Stacked Cage Assembly: EMI Spring



Form Factor: **zSFP+ Stacked (SFP56)**
Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**
Centerline (Pitch): **.6 mm [.018 in]**
Circuit Application: **Signal**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

[All SFP56 Stacked Cage Assembly: EMI Spring \(48\)](#)

Features

Product Type Features

Cage Type	Stacked
Form Factor	zSFP+ Stacked (SFP56)
Pluggable I/O Product Type	Cage Assembly with Integrated Connector

Configuration Features

Number of Positions	20
Number of Ports	24
Port Matrix Configuration	2 x 12

Electrical Characteristics

Data Rate (Max)	56 Gb/s
-----------------	---------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Housing Features

Centerline (Pitch)	.6 mm[.018 in]
--------------------	----------------



Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Pluggable I/O Applications	SFP28
Circuit Application	Signal

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1761394-1
DUST COVER, SFP, GANGED &
STACKED

Also in the Series

SFP56

Pluggable IO Connectors & Cages(53)

SFP, SFP+ & zSFP+(53)

Customers Also Bought

TE Part #1734100-3
Champ050 series,30pos,Au over PdNi

TE Part #1734101-3
Champ050 series,30pos,Au over PdNi

TE Part #6-2213362-2
RCPT ASSY,DIMMABLE
PHOTOCONTROL,150C,3 P

TE Part #1-2170287-1
1X4 CAGE ASSEMBLY, QSFP,SINGLE
SQ LP

TE Part #1934949-1
Tinman 5pr 8col vert rcpt 15mm stack

TE Part #1734375-1
CHAMP .050 HIGH RISE, REVERSED

TE Part #5-1375870-4
RCPT ASSY,12 POS,VERT,0.8MM MI

TE Part #2132529-3
IMP100S,H,V3P6C,LG,REW39,5.5

TE Part #2349202-5
SFP56 STACKED 2X1 RECEPTACLE
ASSEMBLY

TE Part #2007808-2
IMP100S,H,V4P10C,LG,OEW46,4.9



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2349201-6_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2349201-6_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2349201-6_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English