




Product Name:	UL3321 28AWG
Product Discription:	UL3321 28AWG
Specification No.:	SPEC-YK-3321-004
Customer's Name:	

Description					Construction							
Rated Voltage:		600V			Conductor		Stranded Tinned Copper					
Rated Temperature:		150℃			Size(AWG)		28					
Reference Standard:		UL758,UL1581			Construction(±0.008mm)		7/0.127					
Cross Section					Stranded Dia.(mm)Ref.		0.38					
					Insulation Material		XLPE					
					Insulation Color		ANY COLOR					
					Ave Thickness(mm)		0.76					
					Min Thickness(mm)		0.69					
					Insulation Dia.(±0.10mm)		2.00					
Marking					Remark:							
E254881RJ AWM STYLE 3321 28AWG 150℃ 600V VW-1 C RJ AWM I A 150℃ 600V FT1 -LF- ELETECK					8724290 Red		8724300 Blue		8724313 Grey		8724322 Violet	
					8724293 Black		8724303 White		8724316 Yellow			
					8724296 Brown		8724307 Green		8724319 Orange			
Applications					Characteristics					Customer Approva		
For internal wiring of electronic and electrical equipment					Test Item			Standard Value			Seal & Stamp	
					Test Material			XLPE(ROHS)				
					Before Aging	Tensile Strength(Mpa)		≥13.79				
						Elongation(%)		≥300				
					Aging Conduction			180±1℃*168hrs				
Revisions					After Aging	Tensile Strength(Mpa)		≥80% of original			Signature:	
						Elongation(%)		≥80% of original				
					Version	Description	Drawn by	Approved by	Date	Deformation(121±1℃*400g)		
0	New document issue	YanBin	David Lin	07/04/2015	Cold Bend(-10±1℃*4hrs)			No crack				
					Heat Shock(180±1℃*1hr)			No crack				
					Flammability Test			VW-1				
					Max.DC Resistance(20℃ Ω/km)			239				