



**The Professional's Choice**

## SAFETY DATA SHEET

### 1. IDENTIFICATION OF THE MATERIAL AND SUPPLIER

#### 1.1 Product identifier

**Product name** LEAK STOP SPRAY SEAL  
**Synonyms** 8498 - PRODUCT CODE

#### 1.2 Uses and uses advised against

**Uses** LEAK SEALANT

#### 1.3 Details of the supplier of the product

**Supplier name** CRC INDUSTRIES (AUST) PTY LIMITED  
**Address** 9 Gladstone Road, Castle Hill, NSW, 2154, AUSTRALIA  
**Telephone** (02) 9849 6700  
**Fax** (02) 9680 4914  
**Email** [info.au@crcind.com](mailto:info.au@crcind.com)  
**Website** [www.crcindustries.com.au](http://www.crcindustries.com.au)

#### 1.4 Emergency telephone numbers

**Emergency** 13 11 26 (PIC)

### 2. HAZARDS IDENTIFICATION

#### 2.1 Classification of the substance or mixture

CLASSIFIED AS HAZARDOUS ACCORDING TO SAFE WORK AUSTRALIA CRITERIA

##### Physical Hazards

Aerosols - Flammable: Category 1  
Aerosols - Pressurised: Category 1

##### Health Hazards

Skin Corrosion/Irritation: Category 2  
Serious Eye Damage / Eye Irritation: Category 2A  
Specific Target Organ Toxicity (Single Exposure): Category 3 (Respiratory Irritation)  
Specific Target Organ Toxicity (Single Exposure): Category 3 (Narcotic Effects)  
Carcinogenicity: Category 2  
Toxic to Reproduction: Category 1A  
Specific Target Organ Toxicity (Repeated Exposure): Category 2  
Repeated exposure may cause skin dryness or cracking.

##### Environmental Hazards

Aquatic Toxicity (Chronic): Category 2

#### 2.2 GHS Label elements

**Signal word** DANGER

**Pictograms**



## PRODUCT NAME LEAK STOP SPRAY SEAL

### Hazard statements

AUH066	Repeated exposure may cause skin dryness or cracking.
H222	Extremely flammable aerosol.
H229	Pressurized container: may burst if heated.
H315	Causes skin irritation.
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
H336	May cause drowsiness or dizziness.
H351	Suspected of causing cancer.
H360	May damage fertility or the unborn child.
H373	May cause damage to organs through prolonged or repeated exposure.
H411	Toxic to aquatic life with long lasting effects.

### Prevention statements

P201	Obtain special instructions before use.
P202	Do not handle until all safety precautions have been read and understood.
P210	Keep away from heat/sparks/open flames/hot surfaces. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Pressurized container: Do not pierce or burn, even after use.
P260	Do not breathe dust/fume/gas/mist/vapours/spray.
P264	Wash thoroughly after handling.
P271	Use only outdoors or in a well-ventilated area.
P273	Avoid release to the environment.
P280	Wear protective gloves/protective clothing/eye protection/face protection.

### Response statements

P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P340	IF INHALED: Remove to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308 + P313	IF exposed or concerned: Get medical advice/ attention.
P321	Specific treatment is advised - see first aid instructions.
P362	Take off contaminated clothing and wash before re-use.
P391	Collect spillage.

### Storage statements

P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P410 + P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C.

### Disposal statements

P501	Dispose of contents/container in accordance with relevant regulations.
------	--

### 2.3 Other hazards

No information provided.

---

## 3. COMPOSITION/ INFORMATION ON INGREDIENTS

---

### 3.1 Substances / Mixtures

Ingredient	CAS Number	EC Number	Content
HYDROCARBONS, C3-4-RICH, PETROLEUM DISTILLATE (<0.1% W/W 1,3-BUTADIENE)	68512-91-4	270-990-9	30 to 60%
NON HAZARDOUS INGREDIENTS	Not Available	Not Available	Remainder
METHYL ISOBUTYL KETONE	108-10-1	203-550-1	20 to <30%
CYCLOHEXANE	110-82-7	203-806-2	5 to 10%
TOLUENE	108-88-3	203-625-9	5 to 10%

---

## 4. FIRST AID MEASURES

---

### 4.1 Description of first aid measures

<b>Eye</b>	If in eyes, hold eyelids apart and flush continuously with running water. Continue flushing until advised to stop by a Poisons Information Centre, a doctor, or for at least 15 minutes.
<b>Inhalation</b>	If inhaled, remove from contaminated area. To protect rescuer, use a Type A (Organic vapour) respirator or an Air-line respirator (in poorly ventilated areas). Apply artificial respiration if not breathing.

## PRODUCT NAME LEAK STOP SPRAY SEAL

<b>Skin</b>	If skin or hair contact occurs, remove contaminated clothing and flush skin and hair with running water. Continue flushing with water until advised to stop by a Poisons Information Centre or a doctor.
<b>Ingestion</b>	For advice, contact a Poisons Information Centre on 13 11 26 (Australia Wide) or a doctor (at once). If swallowed, do not induce vomiting.
<b>First aid facilities</b>	None allocated.

### **4.2 Most important symptoms and effects, both acute and delayed**

See Section 11 for more detailed information on health effects and symptoms.

### **4.3 Immediate medical attention and special treatment needed**

Treat symptomatically.

---

## **5. FIRE FIGHTING MEASURES**

### **5.1 Extinguishing media**

Dry agent, carbon dioxide or foam. Prevent contamination of drains and waterways.

### **5.2 Special hazards arising from the substance or mixture**

Extremely flammable aerosol. May evolve toxic gases (carbon oxides, hydrocarbons) when heated to decomposition. Aerosol may explode at temperatures exceeding 50°C. Eliminate all ignition sources including cigarettes, open flames, spark producing switches/tools, heaters, naked lights, pilot lights, etc when handling. Aerosol cans may explode when heated above 50°C.

### **5.3 Advice for firefighters**

Evacuate area and contact emergency services. Toxic gases may be evolved in a fire situation. Remain upwind and notify those downwind of hazard. Wear full protective equipment including Self Contained Breathing Apparatus (SCBA) when combating fire. Use waterfog to cool intact containers and nearby storage areas.

### **5.4 Hazchem code**

2YE  
2 Fine Water Spray.  
Y Risk of violent reaction or explosion. Wear full fire kit and breathing apparatus. Contain spill and run-off.  
E Evacuation of people in and around the immediate vicinity of the incident should be considered.

---

## **6. ACCIDENTAL RELEASE MEASURES**

### **6.1 Personal precautions, protective equipment and emergency procedures**

Wear Personal Protective Equipment (PPE) as detailed in section 8 of the SDS. Clear area of all unprotected personnel. Ventilate area where possible.

### **6.2 Environmental precautions**

Prevent product from entering drains and waterways.

### **6.3 Methods of cleaning up**

Contain spillage, then cover / absorb spill with non-combustible absorbent material (vermiculite, sand, or similar), collect and place in suitable containers for disposal.

### **6.4 Reference to other sections**

See Sections 8 and 13 for exposure controls and disposal.

---

## **7. HANDLING AND STORAGE**

### **7.1 Precautions for safe handling**

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

### **7.2 Conditions for safe storage, including any incompatibilities**

Store in a cool (< 50°C), dry, well ventilated area, removed from incompatible substances, heat or ignition sources and foodstuffs. Ensure aerosol containers/ cans are adequately labelled, protected from physical damage and sealed when not in use. Check regularly for damaged/ leaking containers. Large storage areas should have appropriate fire protection systems.

### **7.3 Specific end uses**

No information provided.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

### 8.1 Control parameters

#### Exposure standards

Ingredient	Reference	TWA		STEL	
		ppm	mg/m <sup>3</sup>	ppm	mg/m <sup>3</sup>
Cyclohexane	SWA [AUS]	100	350	300	1050
Cyclohexane	SWA [Proposed]	100	350	--	--
Methyl isobutyl ketone	SWA [AUS]	50	205	75	307
Toluene	SWA [AUS]	50	191	150	574

#### Biological limits

Ingredient	Determinant	Sampling Time	BEI
METHYL ISOBUTYL KETONE	Methyl isobutyl ketone in urine	End of shift	1 mg/L
TOLUENE	o-Cresol in urine (with hydrolysis)	End of shift	0.3 mg/g creatinine
	Toluene in urine	End of shift	0.03 mg/L
	Toluene in blood	Prior to last shift of workweek	0.02 mg/L

Reference: ACGIH Biological Exposure Indices

### 8.2 Exposure controls

**Engineering controls** Avoid inhalation. Use in well ventilated areas. Where an inhalation risk exists, mechanical explosion proof extraction ventilation is recommended. Flammable/explosive vapours may accumulate in poorly ventilated areas. Vapours are heavier than air and may travel some distance to an ignition source and flash back. Maintain vapour levels below the recommended exposure standard.

#### PPE

- Eye / Face** Wear splash-proof goggles.
- Hands** Wear PVA or viton® gloves.
- Body** When using large quantities or where heavy contamination is likely, wear coveralls.
- Respiratory** Where an inhalation risk exists, wear a Type A-Class P1 (Organic gases/vapours and Particulate) respirator.



## 9. PHYSICAL AND CHEMICAL PROPERTIES

### 9.1 Information on basic physical and chemical properties

<b>Appearance</b>	VISCOUS OPAQUE LIQUID (AEROSOL DISPENSED)
<b>Odour</b>	CHARACTERISTIC ODOUR
<b>Flammability</b>	EXTREMELY FLAMMABLE
<b>Flash point</b>	< 0°C (Propellant)
<b>Boiling point</b>	NOT AVAILABLE
<b>Melting point</b>	NOT AVAILABLE
<b>Evaporation rate</b>	NOT AVAILABLE
<b>pH</b>	NOT AVAILABLE
<b>Vapour density</b>	NOT AVAILABLE
<b>Specific gravity</b>	NOT AVAILABLE
<b>Solubility (water)</b>	INSOLUBLE
<b>Vapour pressure</b>	NOT AVAILABLE
<b>Upper explosion limit</b>	NOT AVAILABLE
<b>Lower explosion limit</b>	NOT AVAILABLE
<b>Partition coefficient</b>	NOT AVAILABLE
<b>Autoignition temperature</b>	NOT AVAILABLE
<b>Decomposition temperature</b>	NOT AVAILABLE
<b>Viscosity</b>	NOT AVAILABLE

## PRODUCT NAME LEAK STOP SPRAY SEAL

### 9.1 Information on basic physical and chemical properties

Explosive properties	NOT AVAILABLE
Oxidising properties	NOT AVAILABLE
Odour threshold	NOT AVAILABLE

## 10. STABILITY AND REACTIVITY

### 10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

### 10.2 Chemical stability

Stable under recommended conditions of storage.

### 10.3 Possibility of hazardous reactions

Polymerization will not occur.

### 10.4 Conditions to avoid

Avoid shock, friction, heavy impact, heat, sparks, open flames and other ignition sources.

### 10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites), acids (e.g. nitric acid), alkalis (e.g. sodium hydroxide), heat and ignition sources.

### 10.6 Hazardous decomposition products

May evolve toxic gases (carbon oxides, hydrocarbons) when heated to decomposition.

## 11. TOXICOLOGICAL INFORMATION

### 11.1 Information on toxicological effects

**Acute toxicity** Acute exposure causes dose-related central nervous effects including nausea, vomiting, abdominal pain, diarrhoea, dizziness and drowsiness. This product may have the potential to cause adverse health effects if intentionally misused (e.g. deliberately inhaling contents).

#### Information available for the ingredients:

Ingredient	Oral LD50	Dermal LD50	Inhalation LC50
METHYL ISOBUTYL KETONE	1600 mg/kg (guinea pig); 2080 mg/kg (rat)	> 20 mL/kg (rabbit)	100 mg/L (rat)
CYCLOHEXANE	813 mg/kg (mouse)	--	70 g/m <sup>3</sup> (mammal)
TOLUENE	5580 mg/kg (rat)	5000 mg/kg (rabbit)	25.7 - 30 mg/L/4hrs (rat)

<b>Skin</b>	Irritating to the skin. Contact may result in drying and defatting of the skin, irritation, rash and dermatitis.
<b>Eye</b>	Irritating to the eyes. Contact may result in irritation, lacrimation, pain and redness.
<b>Sensitisation</b>	Not classified as causing skin or respiratory sensitisation.
<b>Mutagenicity</b>	Insufficient data available to classify as a mutagen.
<b>Carcinogenicity</b>	Suspected of causing cancer. Methyl isobutyl ketone is classified as a possible human carcinogen (IARC Group 2B).
<b>Reproductive</b>	Over exposure to toluene may damage fertility or the unborn child.
<b>STOT - single exposure</b>	Over exposure may result in irritation of the nose and throat, coughing, nausea and headache. High level exposure may result in dizziness, drowsiness, breathing difficulties and unconsciousness.
<b>STOT - repeated exposure</b>	Repeated exposure to toluene may result in central nervous system (CNS), liver and kidney damage.
<b>Aspiration</b>	Ingestion is considered unlikely due to product form. However, if liquid component is ingested, aspiration into the lungs may cause chemical pneumonitis and pulmonary oedema.

## 12. ECOLOGICAL INFORMATION

### 12.1 Toxicity

Toxic to aquatic life with long lasting effects.

## PRODUCT NAME LEAK STOP SPRAY SEAL

### 12.2 Persistence and degradability

Cyclohexane is not subject to rapid biodegradation and may be quite persistent. Will volatilise rapidly.

### 12.3 Bioaccumulative potential

Cyclohexane is not considered to be bioaccumulative.

### 12.4 Mobility in soil

If released to soil, cycloheximide is expected to have very high mobility based upon an estimated Koc of 47.

### 12.5 Other adverse effects

If aromatic hydrocarbons are released to soil, they will evaporate from near-surface soil & leach to groundwater. Biodegradation occurs in soil & groundwater but may be slow, especially at high concentrations, which can be toxic to microorganisms. Will exist largely as vapour in air. Half life in atmosphere depends on particular hydrocarbon (eg 1-2 days (xylene); 3 hrs-1 day (toluene)).

---

## 13. DISPOSAL CONSIDERATIONS

---

### 13.1 Waste treatment methods

**Waste disposal** For small amounts, absorb contents with sand or similar and dispose of to an approved landfill site. Do not puncture or incinerate aerosol cans. Contact the manufacturer/supplier for additional information (if required).

**Legislation** Dispose of in accordance with relevant local legislation.

---

## 14. TRANSPORT INFORMATION

---

CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE



	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
<b>14.1 UN Number</b>	1950	1950	1950
<b>14.2 Proper Shipping Name</b>	AEROSOLS	AEROSOLS	AEROSOLS
<b>14.3 Transport hazard class</b>	2.1	2.1	2.1
<b>14.4 Packing Group</b>	None allocated.	None allocated.	None allocated.

### 14.5 Environmental hazards

Marine Pollutant.

### 14.6 Special precautions for user

**Hazchem code** 2YE

**GTEPG** 2D1

**EmS** F-D, S-U

**Other information** The environmentally hazardous substance mark is not required when transported in packages of less than 5 kg/L (UN Model Regulations: Special Provision 375; IATA: Special Provision A197; IMDG: Special Provision 969) or less than 500 kg/L by Australian Road and Rail.

---

## 15. REGULATORY INFORMATION

---

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

**Poison schedule** Classified as a Schedule 5 (S5) Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).

**Classifications** Safework Australia criteria is based on the Globally Harmonised System (GHS) of Classification and Labelling of Chemicals.

**Inventory listings** **AUSTRALIA: AIIC (Australian Inventory of Industrial Chemicals)**  
All components are listed on AIIC, or are exempt.

## 16. OTHER INFORMATION

**Additional information** AEROSOL CANS may explode at temperatures approaching 50°C.

**PERSONAL PROTECTIVE EQUIPMENT GUIDELINES:**

The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as form of product, method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.

**HEALTH EFFECTS FROM EXPOSURE:**

It should be noted that the effects from exposure to this product will depend on several factors including: form of product; frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.

**Abbreviations**

ACGIH	American Conference of Governmental Industrial Hygienists
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds
CNS	Central Nervous System
EC No.	EC No - European Community Number
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)
GHS	Globally Harmonized System
GTEPG	Group Text Emergency Procedure Guide
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration, 50% / Median Lethal Concentration
LD50	Lethal Dose, 50% / Median Lethal Dose
mg/m <sup>3</sup>	Milligrams per Cubic Metre
OEL	Occupational Exposure Limit
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).
ppm	Parts Per Million
STEL	Short-Term Exposure Limit
STOT-RE	Specific target organ toxicity (repeated exposure)
STOT-SE	Specific target organ toxicity (single exposure)
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons
SWA	Safe Work Australia
TLV	Threshold Limit Value
TWA	Time Weighted Average

**Report status**

This document has been compiled by RMT on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It is based on information concerning the product which has been provided to RMT by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

While RMT has taken all due care to include accurate and up-to-date information in this SDS, it does not provide any warranty as to accuracy or completeness. As far as lawfully possible, RMT accepts no liability for any loss, injury or damage (including consequential loss) which may be suffered or incurred by any person as a consequence of their reliance on the information contained in this SDS.

**Prepared by**

Risk Management Technologies  
 5 Ventnor Ave, West Perth  
 Western Australia 6005  
 Phone: +61 8 9322 1711  
 Fax: +61 8 9322 1794  
 Email: info@rmt.com.au  
 Web: www.rmtglobal.com

**[ End of SDS ]**