

Coupling - VS-MP-PPC/CG-FO - 1404319

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Multi-port data connection: push/pull SC-RJ, for passive PROFINET cabling to robots, including mounting foot.

Product description

Push/pull power and data coupling; version 14



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 709699
Weight per Piece (excluding packing)	253.6 g
Custom tariff number	85366990
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Mechanical characteristics

Connection profile	Data: SCRJ
Insertion/withdrawal cycles	≥ 500 (Data)
Max. cable diameter	5 mm ... 8 mm (Data cable gland)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 70 °C
Degree of protection	IP65

Material data

Housing material	Aluminum press-drawn section / die-cast zinc
------------------	--

Classifications

eCl@ss

eCl@ss 4.0	272607xx
------------	----------

Coupling - VS-MP-PPC/CG-FO - 1404319

Classifications

eCl@ss

eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

ETIM

ETIM 3.0	EC000830
ETIM 4.0	EC001134
ETIM 5.0	EC001134

UNSPSC

UNSPSC 6.01	26121616
UNSPSC 7.0901	26121616
UNSPSC 11	26121604
UNSPSC 12.01	31261501
UNSPSC 13.2	26121616

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted


Approval details

EAC

Drawings

Coupling - VS-MP-PPC/CG-FO - 1404319

Drilling diagram



Dimensioned drawing

