



6 PC Brushless Combo Kit LXT®

DLX6131TX1

18V

Includes: DHP484, DTD153, DHR242, DGA463, DTM52,
DML815, DC18RC and 3x BL1850B



Models in kit



Combi Drill LXT®
DHP484



Rotary Hammer LXT®
DHR242



115mm Grinder LXT®
DGA463



LED Flashlight LXT®
DML815



Multi Tool LXT®
DTM52



Impact Driver LXT®
DTD153

Combi Drill LXT®

DHP484

18V • 54 Nm • 0 – 2 000 min⁻¹

A powerful, brushless general-use impact drill for screwdriving and drilling

An efficient, brushless drill for professional screwdriving and drilling with or without hammer action, two power settings. Max. torque of 54 / 30 Nm. A versatile tool for fitters, builders and maintenance staff. Integrated LED light.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Electronic brake	✓
No load speed	0 - 500 / 2000 min ⁻¹
Max. fastening torque Hard/Soft	54 / 30 Nm
Max Torque	65 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 7500 / 30000 min ⁻¹
Max. Drilling Diameter in Masonry	13 mm
Max. Drilling Diameter in Concrete	13 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	38 mm
Drilling Capacity Wood (Self-feed bit)	38 mm
Drilling Capacity Flat bit	38 mm

User benefits

- Brushless maintenance-free and long-life motor
- With impact mode, the tool can be used for drilling stone materials.
- Ergonomic soft grip handle provides increased comfort
- LED light illuminates the work site
- Electronic overload protection protects the user and the device
- All metal gear construction ensures high transmission durability
- Mechanical 2-speed gearing; High speed mode for speedy drilling in light duty applications; Low speed mode for heavy duty applications requiring high torque
- Electric brake for maximum productivity and increased operator safety
- Reversing switch is conveniently located
- Highly efficient and compact machine for professional use
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Rotary Hammer LXT®

DHR242Z

18V • SDS-PLUS • 24 mm • 2.0 J

Professional brushless, three-mode rotary hammer

An efficient rotary hammer for SDS-PLUS bits with an anti-vibration handle. Suitable for impact and unstressed drilling, plus chipping. Speed range of 0 – 950 min⁻¹. Impact energy of 2.0 J and max. drilling capacity of 24 mm in concrete. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 950 min ⁻¹
Impacts per Minute (IPM)	0 - 4700 min ⁻¹
Max. Drilling Diameter in Concrete	24 mm
Optimum Drilling Diameter Range in Concrete	4 - 16 mm
Drilling diameter with TCT core bit	54 mm
Max. Drilling Diameter in Steel	13 mm
Max. Drilling Diameter in Wood	27 mm
Impact Energy	2,0 J
Adapted for SDS-PLUS bits	✓
Electronic brake	✓
Sound Power Level (L _{WA})	99 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- Low power consumption thanks to brushless motor
- Battery protection circuit protects against overloading, over-discharging and over-heating

EAN 0088381654326

Link to product - www.makita.uk.com



Angle Grinder LXT®

DGA463Z

18V • 115 mm • 3 000 – 8 500 min⁻¹

Powerful angle grinder

A 18V powerful cordless angle grinder. The Angle grinder can be connected to a dust extraction system with optional dust-collecting wheel cover. Anti-restart function and standard angle grinder discs available.



LXT **BL** **ADT** **AFT** **BRAKE**

Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	3000 - 8500 min ⁻¹
Spindle Thread	M14
Bore Size (Arbor Diameter)	22,23 mm
Anti-Restart Function (NVR Switch)	✓
Electronic brake	✓
Disc Diameter	115 mm
Sound Power Level (L _{WA})	90 dB(A)
Sound Pressure Level (L _{pA})	82 dB(A)
Product net weight	1,6 kg
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,3 - 3,8 kg
Product Dimensions (L x W x H):	362 x 130 x 145

User benefits

- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Compact and lightweight design
- Electric brake for maximum productivity and increased operator safety
- Brushless motor eliminates carbon brushes, enabling the Brushless motor to run cooler and more efficiently for longer life
- 3-stage LED gauge indicates battery charge level / overheating / overload
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381853514

Link to product - www.makitauk.com



Multi tool LXT®

DTM52Z

18V • 10 000 - 20 000 min⁻¹

Multi-tool for cutting, polishing, grout removal and other applications.

A handy 18V LXT® multi-function tool for a variety of cutting and polishing applications in construction and renovation projects, compatible with STARLOCK MAX. Equipped with a tool-less accessory clamp and the oscillating rate can be adjusted between 10 000 and 20 000 min⁻¹. Tool only, battery and a charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Orbits per Minute	10000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,8 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	72 - 79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,7 - 2,0 kg
Vibration Level, Sanding	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Product Dimensions (L x W x H):	332 x 95 x 125 mm
Vibration Level, Cutting With Plunge Cut Saw Blade	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting With Plunge Cut Saw Blade	1,5 m/s ²

User benefits

- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Soft start for smooth start-ups
- Anti-restart function minimises accidental start-up
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- 12 Angle settings at every 30° from 0° to 360°

EAN 0088381741316

Link to product - www.makita.uk.com





Impact Driver LXT®

DTD153Z

18V • 1/4" • 170 Nm • 0 – 3 400 min⁻¹

Extra-compact brushless impact driver for quick driving

A compact and light brushless impact driver with a hex. 1/4" drive shank. A small and light tool that is easy to use but offers a max. fastening torque of 170 Nm, suitable for quick driving. A handy LED light for added lighting. Tool only, battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 3400 min ⁻¹
Max Fastening Torque Impact Drill	170 Nm
Tightening Capacity Standard Bolt	M5 - M16
Impacts per Minute (IPM)	0 - 3600 min ⁻¹
Driving Shank	1/4 "
Sound Power Level (L _{WA})	107 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	13,0 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

EAN 0088381823883

Link to product - www.makitauk.com

User benefits

- Low power consumption thanks to brushless motor
- The rubber coating on the handle ensures a firm working grip
- The screw tip is securely held in place by a quick lateral stroke
- LED light illuminates the work site
- Quick mount for 1/4 "screwdriver
- Battery protection system automatically shuts off power when the battery level is low
- Variable speed control dial enables user to match the speed to the application for greater versatility



LED Light LXT®

DML815

14,4V / 18V • 3000 lx

Handy and efficient light

A lamp for 14.4V and 18V batteries. Light and easily portable. Equipped with a four LED bulb that offers extremely bright lighting. The run time with a 5.0Ah battery is about 25 h.



Technical specifications

Nominal Battery Voltage	14,4 / 18 V
Voltage LXT	✓
Luminous flux	160 Lumen
Illuminance	3000 lx
LED wattage	0,5 W
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Continuous Use 14.4V / 3.0 Ah Battery	17 h
Continuous Use 18V / 1.5 Ah Battery	10,5 h
Continuous Use 18V / 3.0 Ah Battery	24,5 h
Continuous Use 18V / 6.0 Ah Battery	54 h
Angle range vertical	170 °
Tool weight with battery	0,56 - 0,93 kg
Product Dimensions (L x W x H):	272 x 79 x 116 mm

User benefits

- The rubber coating on the handle ensures a firm working grip
- 12 position pivoting flashlight head
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381886970

Link to product - www.makita.uk.com

