

FEATURES

- **Flush cut type:** Ensures precise and clean cuts, reducing the need for additional finishing
- **High carbon steel jaws:** Offers durability and long-lasting performance
- **Bi-material dolphin handle:** Provides ergonomic comfort and improved grip
- **ESD safe:** Suitable for use in electrostatic-sensitive environments
- **Maximum cutting capacity of 1.3 mm:** Capable of handling a variety of wire sizes
- **Overall length of 138 mm:** Compact design for easy handling and storage

RS PRO Bi-Material Dolphin Handle Flush Cutter, High Carbon Steel Jaws

RS Stock No: 616-313



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO Flush Cutter is designed for precision cutting of copper and ferrous wires. Its flush cut type ensures clean and accurate cuts, making it ideal for electronics and electrical applications. The bi-material dolphin handle provides comfort and control, enhancing user efficiency.

General Specifications

Application	Copper Wire, Ferrous Wire
Cut Type	Flush
Handle Material	Bi-Material Dolphin
Height Safe	No
Jaw Material	High Carbon Steel
Product Type	Flush Cutter
Sub Type	Flush Cutter

Protection Category

ESD Safe	Yes
Non-Sparking	No
VDE/1000V Approved	No

Mechanical Specifications

Maximum Cutting Capacity	1.3 mm
Overall Length	138 mm

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, IEC 61340-5-1, REACH, RoHS
---------------------	--

