

# Eaton 231817

Catalog Number: 231817

Eaton Moeller® series DILER Contactor relay, 42 V 50 Hz, 48 V 60 Hz, N/O = Normally open: 3 N/O, N/C = Normally closed: 1 NC, Spring-loaded terminals, AC operation

### General specifications



Product Name	Catalog Number
Eaton Moeller® series DILER Control relay	231817
	EAN
	4015082318178
Product Length/Depth	Product Height
52 mm	58 mm
Product Width	Product Weight
45 mm	0.17 kg

### Certifications

CE  
UL Category Control No.: NKCR  
IEC/EN 60947-4-1  
EN 60947-5-1  
CSA File No.: 012528  
IEC/EN 60947  
VDE 0660  
CSA  
CSA-C22.2 No. 14-05  
UL 508  
UL File No.: E29184  
CSA Class No.: 3211-03  
UL

## Features & Functions

### Features

Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module

### Fitted with:

Interlocked opposing contacts

## General

### Application

Contactor relays

### Lifespan, mechanical

10,000,000 Operations (AC operated)

### Mounting method

DIN-rail/screw

### Mounting position

As required (except vertical with terminals A1/A2 at the bottom)

### Operating frequency

9000 Operations/h

### Overvoltage category

III

### Pollution degree

3

### Product category

DILER Mini-contactors

### Protection

Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)

### Rated impulse withstand voltage (Uimp)

6000 V AC

### Shock resistance

10 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

8 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

### Voltage type

AC

## Climatic environmental conditions

### Ambient operating temperature - min

-25 °C

### Ambient operating temperature - max

50 °C

## Terminal capacities

### Terminal capacity (flexible with ferrule)

1 x (1 - 2.5) mm<sup>2</sup>

2 x (1 - 2.5) mm<sup>2</sup>

### Terminal capacity (solid/stranded AWG)

Ambient operating temperature (enclosed) - min  
25 °C

Ambient operating temperature (enclosed) - max  
40 °C

Climatic proofing

Damp heat, cyclic, to IEC 60068-2-30

Damp heat, constant, to IEC 60068-2-78

2 x (16 - 14)

1 x (16 - 14)

Stripping length (main cable)

10 mm

Screwdriver size

0.6 x 3.5 mm, Spring-loaded terminals

Electrical rating

Rated operational voltage (Ue) at AC - max

600 V

Rated insulation voltage (Ui)

690 V

Rated operational current (Ie)

0.5 A at 220 V, DC L/R ≤ 15 ms (with 3 contacts in series)

2.5 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series)

1.5 A at 110 V, DC L/R ≤ 15 ms (with 3 contacts in series)

2.5 A at 60 V, DC L/R ≤ 15 ms (with 2 contacts in series)

10 A

Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V

6 A

Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V

3 A

Rated operational current (Ie) at AC-15, 500 V

1.5 A

Safe isolation

300 V AC, Between coil and auxiliary contacts, According to EN 61140

300 V AC, Between auxiliary contacts, According to EN 61140

Short-circuit rating

Short-circuit protection rating

10 A fast, 500V, Maximum fuse, Short-circuit rating without welding, Contacts

Short-circuit protection rating without welding

6 A gG/gL, 500 V, Max. Fuse, Contacts

Switching capacity

Switching capacity (auxiliary contacts, general use)

10 A, 600 V AC, (UL/CSA)

0.5 A, 250 V DC, (UL/CSA)

Switching capacity (auxiliary contacts, pilot duty)

A600, AC operated (UL/CSA)

## Magnet system

### Duty factor

100 %

### Pick-up voltage

0.8 - 1.1 V AC x  $U_c$  (voltage tolerance - single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz)

0.85 - 1.1 V AC x  $U_c$  (voltage tolerance - dual frequency coil 50/60 Hz)

### Power consumption, pick-up, 50 Hz

25 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

### Power consumption, pick-up, 60 Hz

25 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

### Power consumption, sealing, 50 Hz

4.6 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

1.3 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

### Power consumption, sealing, 60 Hz

1.3 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

### Rated control supply voltage ( $U_s$ ) at AC, 50 Hz - min

42 V

### Rated control supply voltage ( $U_s$ ) at AC, 50 Hz - max

42 V

### Rated control supply voltage ( $U_s$ ) at AC, 60 Hz - min

48 V

### Rated control supply voltage ( $U_s$ ) at AC, 60 Hz - max

48 V

### Rated control supply voltage ( $U_s$ ) at DC - min

0 V

### Rated control supply voltage ( $U_s$ ) at DC - max

0 V

### Switching time (AC operated, make contacts, closing delay) - min

14 ms

### Switching time (AC operated, make contacts, closing delay) - max

21 ms

Switching time (AC operated, make contacts, opening delay) - min

8 ms

Switching time (AC operated, make contacts, opening delay) - max

18 ms

Switching time (AC operated, N/O, with auxiliary contact module, closing delay)

45 ms

## Contacts

Code number

31E

Control circuit reliability

$< 2 \lambda, < 1$  failure at 100,000,000 Operations (at  $U_e = 24$  V DC,  $U_{min} = 17$  V,  $I_{min} = 5.4$  mA)

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

1

Number of auxiliary contacts (normally open contacts)

3

## Design verification

Equipment heat dissipation, current-dependent  $P_{vid}$

0 W

Heat dissipation capacity  $P_{diss}$

0 W

Heat dissipation per pole, current-dependent  $P_{vid}$

0.4 W

Rated operational current for specified heat dissipation ( $I_n$ )

6 A

Static heat dissipation, non-current-dependent  $P_{vs}$

1.8 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

## Resources

Catalogs

Product Range Catalog Switching and protecting motors

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Switching and protecting motors - catalog

Characteristic curve

[eaton-contactors-diler-relay-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-00004748.pdf](#)

[DA-DC-00004763.pdf](#)

Drawings

[eaton-contactors-diler-dimensions.eps](#)

[eaton-contactors-diler-dimensions-002.eps](#)

[eaton-tripping-devices-mounting-diler-contactor-relay-symbol.eps](#)

eCAD model

[ETN.231817.edz](#)

Installation instructions

[IL03407009Z](#)

mCAD model

[DA-CS-dil\\_em\\_c](#)

[DA-CD-dil\\_em\\_c](#)

System overview

#### 10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.2.7 Inscriptions

Meets the product standard's requirements.

#### 10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.4 Clearances and creepage distances

Meets the product standard's requirements.

#### 10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

#### 10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

#### 10.8 Connections for external conductors

Is the panel builder's responsibility.

#### 10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

#### 10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

#### 10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

#### 10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

#### 10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

#### 10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.  
All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)