



DEWALT 10.8V XR Li-Ion Hammer Drill

DCD716D2-GB



- Hammer function provides greater versatility up to 22500bpm for drilling into masonry
- 2 speed gearbox for a greater range of applications
- 16 adjustable torque controls for optimised precision when Screwdriving
- 10mm ratcheting keyless chuck with automatic spindle lock
- Compact body enables operation in confined spaces
- Integrated LED will help illuminate and improve visibility when drilling

Description:

The DEWALT 10.8V XR Hammer Drill has been engineered to be heavy duty yet designed to be ultra-compact. The lightweight design makes this drill perfect for use within confined spaces. It features 16 adjustable torque positions for consistent screwdriving into a variety of materials with different screw sizes. The hammer drill function is ideal for light drilling into masonry and concrete. The ergonomic rubber overmould handle helps reduce fatigue during repetitive usage. Its 10mm keyless chuck with automatic spindle lock makes changing bits easier and can be done with one hand.

Specification	
Battery Type	Li-Ion
Battery Capacity	2.0 Ah
Voltage	10.8 V
Power Output	180 W
Number of Gears	2
Chuck Size	10 mm
Hammer Action	Yes
Drilling Capacity (Masonry)	8 mm
Drilling Capacity (Metal)	10 mm
Drilling Capacity (Wood)	20 mm
No Load Speed	0-400/1500 rpm
Beats Per Minute	0-6000/22500 bpm

Supplied With:

- 2 x 10.8V XR Li-Ion Batteries
- Multi voltage charger
- Heavy Duty Kitbox