

Part Number : 1300108037

Product Description : Mini-Change Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Gray PUR Cable, 2.0m (6.56') Length



Series Number : 130010

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 115033B21M020

---

## Documents & Resources

### Drawings

1300108037\_sd.pdf

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 AWG, Gray PUR Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	FF
Type	Double Ended
UPC	887191260815

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

### Physical

Cable Diameter	12.70mm (.500")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	313.961/g

Orientation	90° to 90°
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 20233
Wire Size (AWG)	16

---

---

This document was generated on Mar 27, 2025