



proximity sensor SME-10M-ZS-24V-E-2,5-L-OE

Part number: 551369

★ Core product range

FESTO



Data sheet

Feature	Value
Design	for round slot
Conforms to standard	EN 60947-5-2
Authorisation	C-Tick
CE mark (see declaration of conformity)	to EU directive for EMC
Special characteristics	Oil resistant
Materials note	Free of copper and PTFE Conforms to RoHS Halogen-free
Measured variable	Position
Measuring principle	Reed magnetic
Ambient temperature	-40 ... 70 °C
Switch output	with contact, bipolar
Switching element function	Normally open contact
Switching output repetition accuracy in ± mm	0.1 mm
Switch-on time	<= 1.2 ms
Switch-off time	<= 1 ms
Max. switching frequency	50 Hz
Max. output current	100 mA
Max. output current in mounting kits	50 mA
Max. contact rating AC	3 VA
Max. contact rating DC	9 W
Max. switching capacity DC in mounting kits	1.5 W
Max. switching capacity AC in mounting kits	1.5 VA
Voltage drop	<= 4.5 V
Short circuit strength	No
Overload withstand capability	Not available
Nominal operating voltage DC	24 V
Operating voltage range AC	5 ... 30 V
Operating voltage range DC	5 ... 30 V
Polarity protected	Bipolar
Electrical connection 1, connection type	Cable
Electrical connection 1, connection technology	Open end
Electrical connection 1, number of pins/wires	2
Connector exit direction	axial
Test conditions of cable	Bending strength according to Festo standard Test conditions on request Chain link trunking: 5 million cycles, bending radius 28 mm Torsion resistance: > 300,000 cycles, ±270°/0.1 m
Cable length	2.5 m
Cable attribute	Energy chain + robot
Material cable sheath	TPE-U(PUR)
Mounting type	Tightened Insertable in slot from above
Max. tightening torque	0.4 Nm

Feature	Value
Assembly position	Any
Product weight	14.6 g
Material housing	PA-reinforced High alloy steel, non-corrosive
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-20 ... 70 °C
Protection class	IP65 IP68