





Technical data

N209

Single row cylindrical roller bearings

Single row cylindrical roller bearing, floating, separable, pressed steel cage

VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	45 mm
D - External diameter	85 mm
B - Bearing/Inner ring width	19 mm
E - Upper roller diameter	75 mm
F - Under roller diameter	55 mm
d1 - IR flange outer diameter	59 mm
rs - Min fillet radius	1,1 mm
r1s - Min fillet radius	1,1 mm
Radial clearance class	CN
Mass	0,423 kg

PRODUCT PERFORMANCE	
C - Dynamic load	51000000 mN
C0 - Static load	47000000 mN
Cu - Fatigue limit load	5700000 mN
N lim - Oil lubrication limit speed	59400 °/s
N lim - Grease lubrication limit speed	50400 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT	
da min - Min shoulder diameter IR	51,5 mm
Da max - Max shoulder diameter OR	78,5 mm
Db min - Small face shoulder min diameter	76 mm



N209

Single row cylindrical roller bearings

ABUTMENT	
Dc max - Max outer ring GO diameter	73 mm
ra max - Max fillet radius	1 mm
r1a - Max fillet radius	1 mm

INDUSTRY CALCUL FACTORS
Equivalent dynamic radial load $P = Fr$
Equivalent static radial load $P_0 = Fr$

