



Part Number : [2059260010](#)

Product Description : MultiCat Mid-Power Receptacle Housing, 8 Circuits, Key A, Black, without CPA

Series Number : 205926

Status : Active

Product Category : Connector Housings

Engineering Number : 2059260010-FCT



Documents & Resources

Drawings

[2059260010 sd.pdf](#)

[2059260000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications


[2059250000-AS-000.pdf](#)

[2059250000-PS-000.pdf](#)

[2059250000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	205926
Description	MultiCat Mid-Power Receptacle Housing, 8 Circuits, Key A, Black, without CPA
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	MultiCat
UPC	191130501397

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Resin	PEI
Net Weight	4.823/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.60mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +150°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MultiCat Mid-Power Plug Housings	<u>205925</u>
MultiCat Mid-Power Vertical Headers	<u>205927</u>

Use with Part(s)

Description	Part Number
MultiCat Mid-Power Female Crimp Terminals	<u>202936</u>