

**FAG****6036-M-C3**

Deep groove ball bearing

Deep groove ball bearing 60...-M, single row,
solid brass cage

Technical information



Your current product variant

Sealing	Without	Not sealed
Cage	M	Solid brass cage, rolling element guided
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	S1	Rings dimensional stabilized up to 200°
Lubricant	Without	Bearing not greased
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	180 mm	Bore diameter
D	280 mm	Outside diameter
B	46 mm	Width
C _r	201,000 N	Basic dynamic load rating, radial
C _{0r}	199,000 N	Basic static load rating, radial
C _{ur}	8,400 N	Fatigue load limit, radial
n _G	4,050 1/min	Limiting speed
n _{gr}	3,300 1/min	Reference speed
≈m	10.6 kg	Weight



Mounting dimensions

d _{a min}	190.2 mm	Minimum diameter shaft shoulder
D _{a max}	269.8 mm	Maximum diameter of housing shoulder
r _{a max}	2.1 mm	Maximum fillet radius

Dimensions

r _{min}	2.1 mm	Minimum chamfer dimension
D ₁	249.25 mm	Shoulder diameter outer ring
d ₁	211.8 mm	Shoulder diameter inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

f ₀	15.6	Calculation factor
----------------	------	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Grease Lubrication
	Oil Lubrication
	Not sealed