




Application Tooling > Insertion & Extraction Tools



Insertion & Extraction Tool Type: **Contact Extraction**

Insertion & Extraction Tool Application: **Contact-to-Wire**

Features

Product Type Features

Insertion & Extraction Tool Type	Contact Extraction
Insertion & Extraction Tool Application	Contact-to-Wire

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1766232-1

CONTACT,PIN, .25 DIA

Customers Also Bought

TE Part #1052902-1

2052 5674 02

TE Part #6648434-1

CONTACT,SKT,SIZE 1/4 (712-81-01107)

TE Part #1648325-1

702-92-01109=CONTACT,SKT,#20

TE Part #1650589-1

903-19-02113=SCREW,SHOULDER,M4

TE Part #1648152-1

241-28-01100

TE Part #6766615-1

293-0091-01100=HSG ASSY W/CLIPS

TE Part #1766274-1

CONTACT,PIN,#0

TE Part #1766283-1

CONTACT,PIN,#4,M5

TE Part #1766232-1

CONTACT,PIN, .25 DIA

TE Part #133421-E

MJ CS ** 8 8 ***** 30 * J 3 133942

Documents



Product Drawings

713-19-00100=REMOVAL TOOL,#4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1643922-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1643922-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1643922-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

CORCOM_DB_SERIES

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English