




Passive Components > Resistors > Through-Hole Resistors > Wirewound Resistor: Horizontal Mount



Resistance Value: 1 Ω

Resistor Type: **Power Resistor**

Element Type: **Wire Wound**

Power Rating: **40 W**

Resistance Class: **Up to 1kΩ**

[All Wirewound Resistor: Horizontal Mount \(156\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	1 Ω
Power Rating	40 W
Resistance Class	Up to 1kΩ
Passive Component Tolerance	5 %

Body Features

Lead Type	Radial-Leaded FASTON
-----------	----------------------

Termination Features

Number of Terminations	2
------------------------	---

Dimensions

Passive Component Dimensions	10.5 x 8 x 18 mm
------------------------------	------------------

Usage Conditions



Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | CGS SQ

SQBW401R0JFASTON

1 ohm, Through-Hole Power Resistor, Wire Wound, 40 W, 5 %, ±300 ppm/°C, Radial-Leaded FASTON, 10.5 x 8 x 18 mm, Loose Piece - Box, CGS SQ




[Through-Hole Resistors\(659\)](#)

Customers Also Bought



TE Part #1-1624323-5
[UPW50 0.1% 5PPM 50K](#)



TE Part #1-1623779-8
[SQB20 22R 5% \(WIRE\)](#)



TE Part #4-1623732-2
[BCHE 7 W 560R 5%](#)



TE Part #4-1625886-4
[1W SM M/OX 5% 82R](#)



TE Part #1624322-7
[UPW25 0.1% 5PPM 50R](#)




TE Part #2176076-2
[TLRS1050 4.0W R001 1% 60PPM 3K RL](#)



TE Part #1-1623819-4
[SBL4 R051 5%](#)



TE Part #7-6437630-3
[AWTA1504 = POWER TOGGLE](#)



TE Part #3-1879663-6
[H8 249R 0.1% 15PPM](#)



TE Part #1879444-1
[TE 100W 1R0 5% Bracket](#)

Documents

Product Drawings

[SQB40 1R0 5% \(WIRE\) 6.35MM FAS](#)

English

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

SQBW401R0JFASTON

1 ohm, Through-Hole Power Resistor, Wire Wound, 40 W, 5 %, ±300 ppm/°C, Radial-Leaded FASTON, 10.5 x 8 x 18 mm, Loose Piece - Box, CGS SQ



English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English