

MISCELLANEOUS TOOLS

▼ AFE SCREW STARTERS FOR SLOTTED AND CROSS-HEADS

☞	Blade tip dimensions mm	Total length mm	ΔΔ g
AFE.1	● 0,46 x 2,6	150	12
AFE.2	● 0,56 x 3,57	200	15



▼ FOUR-CLAW RETRIEVER

826.0


- For recovering small flat components up to Ø 30 mm.
 - Nickel finish.
- ΔΔ: 20 g.



▼ 827 ULTRA-SLIM MAGNETIC RETRIEVERS

- 827.1: Long-reach flexible model. Head Ø 7 mm.
827.2: Ball-joint model. Head Ø 8 mm.

☞	Max lifting capacity g	Length mm	ΔΔ g
827.1	120	530	80
827.2	120	210	26



▼ FLEXIBLE MAGNETIC RETRIEVER

827.M

- Powerful magnet (3 kg).
 - Magnetic flux conductor prevents sticking to sides.
 - Length 560 mm. Adjustable stiffness.
 - Magnet Ø 20 mm.
- ΔΔ: 130 g.



▼ INSPECTION MIRRORS

- Mirror in plastic frame.
- 834: Fixed, rigid.
834.R1: Articulated, flexible.
834.R2: Articulated, flexible.
834A.RT: Articulated, telescopic.



☞	Ø mirror mm	L mm	ΔΔ g
834	24	175	4
834.R1	36	210	13
834.R2	55	360	40
834A.RT	44	210-700	48