

Product datasheet

Specifications



Zone Valve, 15mm, 2-Way, G External, Brass, 0.6kvs

VZ208E-15BP03

EAN Code: 3606489661014

Main

| | |
|--|--|
| Product or component type | Valve |
| Valve type | Zone |
| Device application | Fan coil unit Chilled ceiling Terminal unit |
| Medium compatibility | Glycol 25 % Glycol 30 % Water Glycol 50 % |
| Valve configuration | 2-Way |
| Valve connection type | G External |
| Valve connection size | G 1/2A |
| Body size | 15 mm (1/2 in) |
| Pipe size | 15 mm |
| Flow characteristic | Uncharacterized |
| Flow coefficient | 0.6 kvs 0.69 cv |
| Pressure class | PN16 |
| Pressure fluid max delta P quiet service | 62.05 kPa |
| Pressure fluid max delta P normal life | 255.1 kPa |
| Seat leakage | Port A: Class IV-S1 (0.005 %) |
| Stem movement | Linear |
| Trim material | Brass |
| Body material | Brass |
| Stem material | Stainless steel AISI 303 |
| Seating seal material | Port A:EPDM (ethylene propylene diene monomer) |
| Stem seal material | EPDM (ethylene propylene diene monomer) |
| Targeted region | Europe Asia Pacific. Australia. |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.4 cm |

| | |
|------------------|--------|
| Package 1 Width | 6.8 cm |
| Package 1 Length | 3.4 cm |
| Package 1 Weight | 140 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|


Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

|  Materials and Substances | |
|---|--|
| Recycled metal content at CR level | 0 |
| Packaging made with recycled cardboard | Yes |
| Packaging without single use plastic | No |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| REACH Regulation | REACH Declaration |

Use Again

|  Repack and remanufacture | |
|---|--|
| Circularity Profile | No need of specific recycling operations |
| Take-back | No |