

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 8-position, shielded, Socket angled M12 Push-Pull, coding: A, Crimp connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 4.5 mm ... 7.5 mm, without crimp contacts

Your advantages

- Plug and Produce: convenient and secure connection, thanks to the manufacturer-independent locking system
- Extremely compact, thanks to the small wiring space and high contact density
- Clear feedback: the connector springs back when not snapped into place correctly
- Safely shielded: reliable shield connection even under extreme mechanical strain
- Robust connection: suitable for railway applications with high shock and vibration loads

Commercial data

Item number	1319948
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	AF2CJN
GTIN	4063151604561
Weight per piece (including packing)	41.8 g
Weight per piece (excluding packing)	22.22 g
Country of origin	DE

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Technical data

Notes

Assembly note

NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

Mounting

Assembly note

Contacts can be clipped in place and unclipped without tools

Product properties


Product type	Circular connector (cable-side)
Sensor type	Universal
Number of positions	8
No. of cable outlets	1
Shielded	yes
Coding	A
Cable outlet	angled

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Dimensions

Dimensional drawing



Wrench size, union nut

15 mm

Wrench size, counter nut

14 mm

External dimensions

Outside diameter

4.5 mm ... 7.5 mm

Housing

Diameter housing

22 mm

Material specifications

Flammability rating according to UL 94	V0
Seal material	NBR

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Material of grip body	Zinc die-cast, nickel-plated
Material for screw connection	Zinc die-cast, nickel-plated

Connection data

Conductor connection

Connection method	Crimp connection
Connection cross section	0.14 mm ² ... 0.34 mm ² (flexible)
Connection cross section AWG	26 ... 22 (flexible)
Stripping length of the individual wire	4 mm +0,5 mm
Tightening torque	1.5 Nm (Screw plug insert with sleeve housing as far it will go)
	4 Nm (Pressure nut with coupling sleeve)

Electrical properties

Rated surge voltage	0.8 kV
Insulation resistance	≥ 100 MΩ
Nominal voltage U _N	30 V AC
	30 V DC
Nominal current I _N	2 A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	-------

Connector

Connection 1

Head design	Socket
Head cable outlet	angled
Head thread type	M12
Head locking type	Push-Pull
Coding	A

Cable/line

Signal type/category	Universal
Stripping length of the individual wire	4 mm +0,5 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-40 °C ... 85 °C (Plug / socket)

Standards and regulations

Standard designation	M12 connector
----------------------	---------------

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Standards/specifications	IEC 61076-2-101
Note	In line with
Standard designation	Shock, vibration
Standards/specifications	EN 50155:2001

SACC-P12FR-8CT-CM SH - Connector


1319948

<https://www.phoenixcontact.com/in/products/1319948>




Drawings

Dimensional drawing



M12 PUSH-PULL female, angled, shielded

Functional drawing



Functional drawing


SACC-P12FR-8CT-CM SH - Connector

1319948

<https://www.phoenixcontact.com/in/products/1319948>



Schematic diagram



M12 PUSH-PULL male pin assignment, 8-pos., socket-side view

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	3.087 kg CO2e

SACC-P12FR-8CT-CM SH - Connector



1319948

<https://www.phoenixcontact.com/in/products/1319948>

Mandatory accessories

CC0,8-TS-0,34F AU - Crimp contact

1319950

<https://www.phoenixcontact.com/in/products/1319950>



Crimp contact, contact diameter: 0.8 mm, turned, Socket, contact material: CuZn, contact surface: Ni/Au, connection cross section: 0.14 mm² ... 0.34 mm², AWG 26 ... 22

Accessories

CRIMPFOX-TC MP - Crimping pliers with digital display

1212510

<https://www.phoenixcontact.com/in/products/1212510>



Crimping pliers, for turned contacts, universal cross section setting, up to a maximum of 2.5 mm², digital display with 0.01 mm increments, pressure lock can be unlocked, including positioning tool

SACC-P12FR-8CT-CM SH - Connector

1319948

<https://www.phoenixcontact.com/in/products/1319948>



MICROFOX-SB - Diagonal cutter

1212489

<https://www.phoenixcontact.com/in/products/1212489>



Electronic diagonal cutter, round head, without chamfer, with opening spring, mirror-polished and oiled, 2-component grip, cutting capacity: soft 0.2 - 2.0 mm; medium hard 1.2 mm; hard 0.5 mm diameter

WIREFOX-D 13 - Stripping tool

1212162

<https://www.phoenixcontact.com/in/products/1212162>



Stripping tool, for stripping installation lines of Ø 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

SACC-P12FR-8CT-CM SH - Connector

1319948

<https://www.phoenixcontact.com/in/products/1319948>



WIREFOX SAC - Stripping tool

1212623

<https://www.phoenixcontact.com/in/products/1212623>



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

VS-CABLE-STRIP-VARIO - Stripping tool

1657407

<https://www.phoenixcontact.com/in/products/1657407>

Stripping tool, for the multi-level stripping of shielded cables



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in