



SAFETY DATA SHEET

InstantFOAM Complete

According to the REACH etc. (Amendment etc.) (EU Exit) Regulations 2020 No. 1577, as amended.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	InstantFOAM Complete
Product number	DIS1000ML, DIS250ML, DIS47ML, DIS400ML, IFS250ML, IFS1000ML, IAF400ML, IFS47ML, 2717, IFS1LTFEN, 2719, 2720, 2718, IFC400RFSC, IFC400RFNL, 2720EX, DIF1247, IFS1LTFNL, DIF12400EX, DIF610EX, FI2720, DIF1200, 6770720, 6770730, 6770736, 6770749, DIX400ML, DIX1L, IFS1LTFDE, DIF610, 2719EX, FI2718, IFS1LTFSC
UFI	UFI: 7QS3-302P-G00V-RRUR

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	PT1 Human Hygiene Biocidal Product
-----------------	------------------------------------

1.3. Details of the supplier of the safety data sheet

Supplier	SC Johnson Professional Ltd Denby Hall Way Denby Derbyshire DE5 8JZ +44 (0) 1773 855100 info.prouk@scj.com
----------	--

1.4. Emergency telephone number

Emergency telephone	National Poisons Information Service (UK) 0344 8920111 (Health Professionals only) National Poisons Information Centre (Eire) 01-8092566/8379964
---------------------	---

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (SI 2019 No. 720)

Physical hazards	Flam. Liq. 2 - H225
Health hazards	Eye Irrit. 2 - H319
Environmental hazards	Not Classified

2.2. Label elements

Hazard pictograms



Signal word	Danger
Hazard statements	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation.

InstantFOAM Complete

Precautionary statements	P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P233 Keep container tightly closed. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P337+P313 If eye irritation persists: Get medical advice/ attention. P404 Store in a closed container. P501 Dispose of contents/ container in accordance with local regulations.
Supplemental label information	BPR001 Use biocides safely. Always read the label and product information before use.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

ETHANOL	80
CAS number: 64-17-5	EC number: 200-578-6
Classification Flam. Liq. 2 - H225 Eye Irrit. 2 - H319	

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Ingestion	Rinse mouth. Promptly get affected person to drink large volumes of water to dilute the swallowed chemical. Never give anything by mouth to an unconscious person. Do not induce vomiting. Get medical attention if any discomfort continues.
Skin contact	Not relevant.
Eye contact	Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention promptly if symptoms occur after washing.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation	No specific symptoms known.
Ingestion	May cause nausea, headache, dizziness and intoxication.
Skin contact	None known.
Eye contact	May cause severe eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	No specific recommendations.
-----------------------------	------------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

InstantFOAM Complete

Suitable extinguishing media Extinguish with the following media: Water spray, fog or mist. Foam, carbon dioxide or dry powder. Dry chemicals, sand, dolomite etc.

5.2. Special hazards arising from the substance or mixture

Specific hazards The product is highly flammable.

Hazardous combustion products Oxides of carbon.

5.3. Advice for firefighters

Protective actions during firefighting Fight fire from safe distance or protected location.

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Environmental precautions Do not discharge into drains or watercourses or onto the ground. Contain spillage with sand, earth or other suitable non-combustible material.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Use explosion-proof electrical equipment. Provide adequate ventilation. Absorb in vermiculite, dry sand or earth and place into containers. Wash thoroughly after dealing with a spillage.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep away from heat, sparks and open flame. Avoid contact with eyes. Good general ventilation should be adequate to control worker exposure to airborne contaminants.

Advice on general occupational hygiene Do not smoke in work area.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in tightly-closed, original container in a dry, cool and well-ventilated place. Keep away from heat, sparks and open flame. Store at temperatures not exceeding 40°C. Take precautionary measures against static discharges.

Storage class Flammable liquid storage.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

ETHANOL

InstantFOAM Complete

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m³

WEL = Workplace Exposure Limit.

Ingredient comments WEL = Workplace Exposure Limits

ETHANOL (CAS: 64-17-5)

Ingredient comments None.

DNEL

Professional - Inhalation; local effects: 1900 mg/m³
 Professional - Dermal; Long term systemic effects: 343 mg/kg/day
 Professional - Inhalation; Long term systemic effects: 950 mg/m³
 Consumer - Inhalation; local effects: 950 mg/m³
 Consumer - Dermal; Long term systemic effects: 206 mg/kg/day
 Consumer - Inhalation; Long term systemic effects: 114 mg/m³
 Consumer - Oral; Long term systemic effects: 87 mg/kg/day

PNEC

- marine water; 0.79 mg/l
 - Fresh water; 0.96 mg/l
 - Intermittent release; 2.75 mg/l
 - STP; 580 mg/l
 - Sediment (Freshwater); 3.46 mg/kg
 - Sediment (Marinewater); 2.9 mg/l
 - Soil; 0.63 mg/kg

COCOGLUCOSIDE (CAS: 68515-73-1)

DNEL

Workers - Inhalation; Long term systemic effects: 420 mg/m³
 Workers - Dermal; Long term systemic effects: 595000 mg/kg/day
 General population - Inhalation; Long term systemic effects: 124 mg/m³
 General population - Dermal; Long term systemic effects: 357000 mg/kg/day
 General population - Oral; Long term systemic effects: 35.7 mg/kg/day

PNEC

- Fresh water; 0.176 mg/l
 - marine water; 0.0176 mg/l
 - Intermittent release; 0.27 mg/l
 - STP; 560 mg/l
 - Sediment (Freshwater); 1.516 mg/kg
 - Sediment (Marinewater); 0.152 mg/kg
 - Soil; 0.654 mg/kg

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Not relevant.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Personal protective equipment that provides appropriate eye and face protection should be worn.

Hand protection

Not applicable.

InstantFOAM Complete

Other skin and body protection	Not relevant.
Hygiene measures	Do not smoke in work area. Promptly remove any clothing that becomes contaminated.
Respiratory protection	Not relevant.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Clear liquid.
Colour	Colourless.
Odour	Alcoholic.
Odour threshold	Not determined.
pH	pH (concentrated solution): 5.0-8.0
Melting point	Not determined.
Initial boiling point and range	Not determined.
Flash point	~ 15.3°C A.9
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	~ 0.844 @ 20°C
Solubility(ies)	Soluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	2.67 mPa s @ 20°C
Explosive properties	Not determined.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

Other information	No information required.
-------------------	--------------------------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
------------	---

10.2. Chemical stability

Stability	No particular stability concerns.
-----------	-----------------------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not known.
------------------------------------	------------

InstantFOAM Complete

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials

Materials to avoid No specific material or group of materials is likely to react with the product to produce a hazardous situation.

10.6. Hazardous decomposition products

Hazardous decomposition products Oxides of carbon.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vivo Does not contain any substances known to be mutagenic.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

Reproductive toxicity

Reproductive toxicity - development Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure No information available.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure No information available.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information No specific health hazards known.

Inhalation No specific health hazards known.

Ingestion May cause nausea, headache, dizziness and intoxication.

Skin contact Skin irritation should not occur when used as recommended.

InstantFOAM Complete

Eye contact Irritating to eyes. Symptoms following overexposure may include the following: Redness. Pain.

Toxicological information on ingredients.

ETHANOL

Acute toxicity - oral

Acute toxicity oral (LD₅₀ mg/kg) 10,470.0

Species Rat

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

ATE oral (mg/kg) 10,470.0

Acute toxicity - dermal

Acute toxicity dermal (LD₅₀ mg/kg) 20,000.0

Species Rabbit

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Acute toxicity inhalation (LC₅₀ vapours mg/l) 117.0

Species Rat

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

ATE inhalation (vapours mg/l) 117.0

Skin corrosion/irritation

Animal data Oedema score: Very slight oedema - barely perceptible (1).

Respiratory sensitisation

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vivo Does not contain any substances known to be mutagenic.

Reproductive toxicity

Reproductive toxicity - development Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure No information available.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure No information available.

Aspiration hazard

InstantFOAM Complete

Aspiration hazard	Based on available data the classification criteria are not met.
General information	No specific health hazards known.
Inhalation	No specific health hazards known.
Ingestion	May cause nausea, headache, dizziness and intoxication.
Skin contact	Skin irritation should not occur when used as recommended.
Eye contact	Irritating to eyes. Symptoms following overexposure may include the following: Redness. Pain.

SECTION 12: Ecological information

Ecotoxicity The product is not expected to be hazardous to the environment.

Ecological information on ingredients.

ETHANOL

Ecotoxicity The product is not expected to be hazardous to the environment.

12.1. Toxicity

Toxicity The product is not expected to be toxic to aquatic organisms.

Ecological information on ingredients.

ETHANOL

Toxicity The product is not expected to be toxic to aquatic organisms.

Acute aquatic toxicity

Acute toxicity - fish LC₅₀, 96 hours: 15300 mg/l, Pimephales promelas (Fat-head Minnow)
LC₅₀, 96 hours: mg/l, Fish

Acute toxicity - aquatic invertebrates EC₅₀, 48 hours: mg/l, Daphnia magna
EC₅₀, : 858 24H mg/l, Marinewater invertebrates
EC₅₀, > 48 hours: 10000 mg/l, Daphnia magna

Acute toxicity - aquatic plants EC₅₀, 72 hours: 275 mg/l, Freshwater algae
IC₅₀, 72 hours: 5000 mg/l, Algae

12.2. Persistence and degradability

Persistence and degradability The product is expected to be biodegradable.

Ecological information on ingredients.

ETHANOL

Persistence and degradability The product is expected to be biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

Ecological information on ingredients.

InstantFOAM Complete

ETHANOL

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient : -0.35

12.4. Mobility in soil

Mobility The product is soluble in water.

Ecological information on ingredients.

ETHANOL

Mobility The product is soluble in water.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

Ecological information on ingredients.

ETHANOL

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

Ecological information on ingredients.

ETHANOL

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information When handling waste, the safety precautions applying to handling of the product should be considered.

Disposal methods This material and its container must be disposed of as hazardous waste. Dispose of waste product or used containers in accordance with local regulations Reuse or recycle products wherever possible.

SECTION 14: Transport information

14.1. UN number

UN No. (ADR/RID) 1170

UN No. (IMDG) 1170

UN No. (ICAO) 1170

UN No. (ADN) 1170

14.2. UN proper shipping name

Proper shipping name (ADR/RID) ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)

InstantFOAM Complete

Proper shipping name (IMDG) ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)

Proper shipping name (ICAO) ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)

Proper shipping name (ADN) ETHANOL SOLUTION (ETHYL ALCOHOL SOLUTION)

14.3. Transport hazard class(es)

ADR/RID class 3

ADR/RID classification code F1

ADR/RID label 3

IMDG class 3

ICAO class/division 3

ADN class 3

Transport labels



14.4. Packing group

ADR/RID packing group II

IMDG packing group II

ICAO packing group II

ADN packing group II

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

EmS F-E, S-D

ADR transport category 2

Emergency Action Code •2YE

Hazard Identification Number 33
(ADR/RID)

Tunnel restriction code (D/E)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

InstantFOAM Complete

EU legislation

REGULATION (EU) No 528/2012 (as amended) concerning the making available on the market and use of biocidal products.

PCS Number 98218

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

General information	Use biocides safely. Always read the label and product information before use.
Key literature references and sources for data	Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet.
Revision comments	NOTE: Lines within the margin indicate significant changes from the previous revision. Revision of information
Revision date	14/09/2021
Revision	22
Supersedes date	07/09/2021
SDS number	20973
Hazard statements in full	H225 Highly flammable liquid and vapour. H319 Causes serious eye irritation.
Notes for Hazard Statements in Full	The full text for Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.