



TG-6050 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Date of issue: 10/14/2015 Revision date: 3/5/2019 Version: 1.4

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : TG-6050 INTERFACE MATERIAL
Product code : TG-6050
Type of product : Thermal interface material, Fillers, putties, plasters, modelling clay

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Fillers
Conductive agents
Function or use category : Conductive agents, Fillers

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

UK

RS Components Ltd
Birchington Road
Corby
Northants
NN17 9RS
Tel: +44 (0) 845 850 9900
Email: RCustomerServicesUK@rs-components.com
Website: www.rs-online.com

Ireland

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
Tel: +353 (0) 1 415 3100
Email: Enquiries.ie@rs-components.com
Website: www.rs-online.com

1.4. Emergency telephone number

Emergency number : +44 1865 407 333 (24hr) +44 1235 239670 (24hr)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

TG-6050 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALUMINA	(CAS-No.) 1344-28-1 (EC-No.) 215-691-6	85	Not classified
SILICONE - A	(CAS-No.) 90337-93-2	15	Not classified

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation	: Inhalation may cause irritation (cough, short breathing, difficulty in breathing).
Symptoms/effects after skin contact	: Causes mild skin irritation.
Symptoms/effects after eye contact	: mild eye irritation.
Symptoms/effects after ingestion	: May cause irritation to the digestive tract. Ingestion may cause nausea and vomiting.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam.
------------------------------	----------------------------------

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire	: Toxic fumes may be released.
--	--------------------------------

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures	: Ventilate spillage area.
----------------------	----------------------------

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	: Mechanically recover the product.
Other information	: Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling	: Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures	: Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Store in a well-ventilated place. Keep cool.
--------------------	--

7.3. Specific end use(s)

No additional information available

TG-6050 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

ALUMINA (1344-28-1)

Germany	TRGS 910 Acceptable concentration notes	
United Kingdom	Local name	Aluminium oxides
United Kingdom	WEL TWA (mg/m ³)	4 mg/m ³ respirable dust 10 mg/m ³ inhalable dust
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station. Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure.

Personal protective equipment:

Protective clothing. Safety glasses. Gloves.

Hand protection:

Protective gloves

Eye protection:

Safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

Personal protective equipment symbol(s):



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: white.
Odour	: odourless.
Odour threshold	: No data available
pH	: Approx. 7
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: > 35 °C
Flash point	: > 93 °C
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

TG-6050 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: Not applicable

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
	pH: Approx. 7
Serious eye damage/irritation	: Not classified
	pH: Approx. 7
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Acute aquatic toxicity	: Not classified
Chronic aquatic toxicity	: Not classified

12.2. Persistence and degradability

ALUMINA (1344-28-1)	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

ALUMINA (1344-28-1)	
Bioaccumulative potential	No bioaccumulation data available.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

TG-6050 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.2. UN proper shipping name				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not applicable

Transport by sea

Not applicable

Air transport

Not applicable

Inland waterway transport

Not applicable

Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

No additional information available

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product