



**Part Number :** [387007504](#)  
**Product Description :** 8.26mm Pitch Beau PCB  
Terminal Strip, without Mounting Ends, Black, 4  
Circuits, with Screw Clamp Washer  
**Series Number :** 38700  
**Status :** Obsolete  
**Product Category :** Terminal Blocks and Barrier  
Strip  
**Engineering Number :** 70504-C-50



## Documents & Resources

### Drawings


[387007504\\_sd.pdf](#)  
[PK-38700-001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Obsolete
Category	Terminal Blocks and Barrier Strip
Series	38700
Description	8.26mm Pitch Beau PCB Terminal Strip, without Mounting Ends, Black, 4 Circuits, with Screw Clamp Washer
Application	Wire-to-Board
Component Type	One Piece
Product Name	Fixed Mount Barrier
Type	Barrier Strips
UPC	800756173092

#### Electrical

Current - Maximum per Contact	20.0A
Voltage - Maximum	300V

#### Physical

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	9.071/g
Number of Rows	1
Orientation	Horizontal
Panel Mount	No
PCB Retention	None
PC Tail Length	3.56mm
Pitch - Mating Interface	N/A
Pitch - Termination Interface	8.26mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Shrouded	Dual-Barrier
Stackable	Yes
Temperature Range - Operating	-40° to +130°C
Termination Interface Style	Through Hole
Wire Size (AWG)	12, 14, 16, 18, 20, 22
Wire Size mm <sup>2</sup>	0.33-3.31

#### Solder Process Data

Lead-Free Process Capability	WAVE
------------------------------	------