

# WT-HF 3,6X140 BK-L - Cable tie

3240746

<https://www.phoenixcontact.com/gb/products/3240746>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, standard version

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240746             |
| Packing unit                         | 1,000 pc            |
| Minimum order quantity               | 1,000 pc            |
| Sales key                            | BE7131              |
| Product key                          | BE7131              |
| Catalog page                         | Page 615 (C-3-2019) |
| GTIN                                 | 4046356704625       |
| Weight per piece (including packing) | 0.6 g               |
| Weight per piece (excluding packing) | 0.54 g              |
| Customs tariff number                | 39269097            |
| Country of origin                    | PL                  |

# WT-HF 3,6X140 BK-L - Cable tie

3240746

<https://www.phoenixcontact.com/gb/products/3240746>



## Technical data

### Product properties

|                      |                |
|----------------------|----------------|
| Product type         | Cable tie      |
| Type                 | Internal teeth |
| Tensile strength GRP | 130 N          |

### Dimensions

|        |        |
|--------|--------|
| Width  | 3.6 mm |
| Length | 140 mm |

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | black (RAL 9005)               |
| Material                               | PA 6.6                         |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Cable/line

|                         |                |
|-------------------------|----------------|
| External cable diameter | 2 mm ... 35 mm |
| Tensile strength        | 130 N          |

### Environmental and real-life conditions

#### Ambient conditions

|                                                 |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Optimum ambient temperature (storage/transport) | 23.00 °C 50.00 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation)                 | -40 °C ... 85 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Ambient temperature (assembly)                  | -10 °C ... 60 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Resistance to UV radiation                      | no                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Short-term temperature                          | 110 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |

### Mounting

|               |                   |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

# WT-HF 3,6X140 BK-L - Cable tie



3240746

<https://www.phoenixcontact.com/gb/products/3240746>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/3240746>

### DNV

Approval ID: TAE00004VK



### UL Recognized

Approval ID: E328576-20210901

# WT-HF 3,6X140 BK-L - Cable tie



3240746

<https://www.phoenixcontact.com/gb/products/3240746>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27140702 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

# WT-HF 3,6X140 BK-L - Cable tie

3240746

<https://www.phoenixcontact.com/gb/products/3240746>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)