


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	47		M	REVISED PER ECO-12-012320	04JUL12	KH	MZ



- 1
- 0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 2
- 0.76μm [.000030] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH A UNIFORM GRADIENT TO 0.25μm [.000010] MIN GOLD PER MIL-G-45204 ON THE REMAINDER OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 3
- 0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN WITH 1.27μm [.000050] MIN MATTE TIN PLATE IN WIRE CRIMP AREA, BOTH OVER 0.76μm [.000030] MIN NICKEL PER QQ-N-290.
- 4
- GOLD PLATING NEED NOT APPEAR IN THIS AREA.
- 5
- WIRE RANGE 26-30 AWG. INSULATION RANGE 1.02 [.040]-1.52 [.060].
- 6
- 0.38μm [.000015] MIN GOLD PER MIL-G-45204 ON MATING END FOR A LENGTH OF 5.08 [.200] MIN, 1.27μm [.000050] MIN TIN-LEAD PER MIL-T-10727 FOR A LENGTH OF 5.69 [.224] MIN ON OPPOSITE END, BOTH OVER 1.27μm [.000050] MIN NICKEL PER QQ-N-290 ON ENTIRE CONTACT.

OBSOLETE	6	1-66424-0	66428-5
	1	66424-8	66428-4
	3	66424-3	66428-3
OBSOLETE	2	66424-1	66428-1
BODY FINISH		STRIP P/N REF	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	7-30-91	TE Connectivity			
		CHK	9-19-91				
DIMENSIONS: mm [INCHES]		APVD	9-20-91	NAME			
		PRODUCT SPEC					
		APPLICATION SPEC		SIZE			
MATERIAL		WEIGHT	-	CAGE CODE		DRAWING NO	
		FINISH		A2 00779		C-66428	
SEE CALLOUTS		SEE CALLOUTS		SCALE		SHEET	
				8:1		1 OF 1	
		CUSTOMER DRAWING		REV		M	