

Features

- Flexible polyurethane (PUR) spiral power cable
- 4-core H07BQ-F TB28 FLEX construction with 1.50 mm² conductors
- 2.8 m extended length with space-saving coiled design
- Tinned copper conductors with EPR/EPDM insulation
- Black polyurethane (PUR) outer sheath
- Operating temperature range: -25°C to +70°C

RS PRO Spiral Cable TB28 FLEX BQ-F power cable 4G1,50mm² , 0.7m / 2.8m Polyurethane (PUR)

RS Stock No.: 327-498



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Spiral Cable H07BQ-F TB28 FLEX power cable is a high-quality spiral cable designed to provide a reliable and durable power connection in applications requiring flexibility and repeated movement. Constructed with 4-core 1.50 mm² conductors, the cable delivers dependable electrical performance and long-term reliability. The conductors are insulated with EPR/EPDM material, while the robust black polyurethane (PUR) outer sheath provides excellent resistance to abrasion, mechanical wear, and frequent flexing, helping to extend service life in demanding environments. The coiled design allows the cable to extend up to 2.8 m when required and retract when not in use, supporting efficient cable management and reducing clutter around equipment and workstations.

This cable is commonly used for connecting movable equipment, machinery, automation systems, and portable electrical devices where flexibility and durability are important. Typical applications include industrial machinery, material handling equipment, production lines, workstations, and power supply connections subject to regular movement. Suitable for operation in temperatures ranging from -25°C to +70°C, the cable is designed to provide reliable power transmission and mechanical protection in industrial and commercial environments where dependable performance is required.

General Specifications

Brand	RS PRO
Product Type	Spiral Cable
Series	TB28 FLEX BQ-F power cable
Number of cores	4
Cable CSA	1,50 mm ²
Shielding	No
Jacket Material	Polyurethane (PUR)
Jacket colour	Black (semi-glossy)
Conductor type	84x0,15 mm Tinned copper
Conductor insulation	EPR/EPDM
Conductor colours	Brown, Black, Grey + Yellow/Green

Mechanical Specifications

Cable diameter	10,20mm
Conductor diameter	3,20mm
Spiral diameter	37,40mm
Retracted spiral cable length	0.7m
Extended spiral cable length	2.8m
Weight	0.86kg
Extension rate	4

Operation Environment Specifications

Minimum operating temperature	-25 °C
Maximum operating temperature	70 °C


Approvals

Compliance/Certifications	RoHS; EN 50525-2-21
---------------------------	---------------------

Dimensional Drawing

*Dimensions below in mm

Key to Standard Diagram	
L	2800
L0	700
ØD	10,2
ØD0	37,4
L1	200
L2	200
L3	
L4	
L5	
L6	



Tolerances $\pm 10\%$ unless stated otherwise