

# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Device connector front mounting, series: CA, straight, shielded: yes, for standard and SPEEDCON interlock, No. of pos.: 17, Direction of rotation: Standard, contact connection type: Pin, Solder connection, Axial seal, Central fastening Pg13,5, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Solder connection: proven connection technology for various litz wires

## Commercial data

Item number	1243871
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRAEL
GTIN	4063151404338
Weight per piece (including packing)	35 g
Weight per piece (excluding packing)	30 g
Customs tariff number	85366990
Country of origin	DE

# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

## Technical data

### Product properties

Product type	Circular connectors (device side)
--------------	-----------------------------------

### Connector

#### Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	17
Direction of rotation	Standard
Connection profile	17
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overvoltage category	III
Degree of pollution	3
Contact diameter <b>Signal contacts</b>	1 mm
Litz wire cross-section <b>Signal contacts</b> max.	1 mm <sup>2</sup>
Nominal current per signal contact	8 A

#### Housing

Order information:	If necessary, order locking nut separately
Housing material	CuZn
Type of locking	for standard and SPEEDCON interlock
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23


### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

## Drawings

Schematic diagram



Connector pin assignment


# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

Dimensional drawing



Installation dimensions

# CA-17P1N126Z00X - Device connector front mounting





1243871

<https://www.phoenixcontact.com/in/products/1243871>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1243871>

 <b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	5 A	18	-

 <b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	48 V	8 A	18	-

<b>cULus Recognized</b>				
-------------------------	--	--	--	--

# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

## Classifications

### ECLASS

ECLASS-11.0	27440109
ECLASS-12.0	27440109
ECLASS-13.0	27440109

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

1243871

<https://www.phoenixcontact.com/in/products/1243871>

## Accessories

### SF-Z0019 - Protective cap

1607449

<https://www.phoenixcontact.com/in/products/1607449>



Plastic protection cap, with eye, IP40 for connectors with M23 external thread, RF, SF series

---

### RC-Z2104X - Metal protective cap

1241739

<https://www.phoenixcontact.com/in/products/1241739>



Metal protective cap, series: RC, UC, RF, SF, NC, RM, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



## CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

### RC-Z2068X - Metal protective cap

1241735

<https://www.phoenixcontact.com/in/products/1241735>

Metal protective cap, series: RC, UC, RF, SF, NC, RM, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)



---

### CA-Z0110 - Color coding

1620700

<https://www.phoenixcontact.com/in/products/1620700>

Color coding, color: green



# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

## CA-Z0111 - Color coding

1620701

<https://www.phoenixcontact.com/in/products/1620701>

Color coding, color: orange



---

## CA-Z0112 - Color coding

1620702

<https://www.phoenixcontact.com/in/products/1620702>

Color coding, color: black



## CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

### CA-Z0001 - Contact removal tool

1620699

<https://www.phoenixcontact.com/in/products/1620699>



Unlocking tool for contact carriers for snapping in the M23 signal device connectors

---

### SACC-E-MU-PG13,5 - Flat nut

1539143

<https://www.phoenixcontact.com/in/products/1539143>



Flat nut, Screw mounting, Pg13.5, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

# CA-17P1N126Z00X - Device connector front mounting



1243871

<https://www.phoenixcontact.com/in/products/1243871>

## PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>

Plastic protective cap, M23, series: M23 PRO



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)