

VDE tweezers 145 mm form 40 serrated


Art.-No.	5-117-VDE
Description	VDE tweezers 145 mm form 40 serrated
Application	Electrician, precision mechanic tweezers
Specification	serrated gripping surface, insulation VDE/GS mark, double triangle DIN IEC60900/EN60900

Material	alloyed tool steel
Surface/Coating	polished, nickel plated, dip insulated
Features	abrasion resistant, insulated, stainless, wear-resistant
Surface resistance	

Shape	NG: Normal tips straight
Icon No.	NG5

Dimensions and weight

A = 16 mm
B = 3 mm
Ai = 19 mm



length 145 mm
weight 39 g

Application and technical data

Mechanic tweezers steel, heavy model, straight round wide with serrations.

With two-color multilayer dip insulation outside red - inside yellow. Damage to the outer red insulation is immediately visible through the yellow insulation underneath. The advantage is a simple and always visible safety control. Our VDE tools are unit-tested according to VDE EN 60900 / IEC 60900, and approved for live working up to 1000 volts. The insulations are REACH-compliant and phthalate-free.