


Apr.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO 85 °C			STORAGE TEMPERATURE RANGE	°C TO °C			
	VOLTAGE	250 V AC			OPERATING HUMIDITY RANGE	% TO %			
	CURRENT	0.5 A			APPLICABLE CABLE				
SPECIFICATIONS									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			○	○
MARKING		CONFIRMED VISUALLY.						○	○
ELECTRIC CHARACTERISTICS									
CONTACT RESISTANCE		100 mA (DC OR 1000 Hz). 1			35 mΩ MAX.			○	○
INSULATION RESISTANCE		500 V DC.			500 MΩ MIN.			○	○
VOLTAGE PROOF		500 V AC FOR 1 min.			NO FLASHOVER OR BREAKDOWN.			○	○
MECHANICAL CHARACTERISTICS									
INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.			7.9 N MIN. 29.4 N MAX.			○	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS. 1			① CONTACT RESISTANCE: 35 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			○	—
VIBRATION		FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s ² AT 2 h, FOR 3 DIRECTIONS.			NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			○	—
SHOCK		490 m/s ² DURATION OF PULSE 11 ms AT 3 TIMES FOR 6 DIRECTIONS.						○	—
ENVIRONMENTAL CHARACTERISTICS									
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → 5~35 → 85 → 5~35 °C TIME 30 → 2~3 → 30 → 2~3 min UNDER 5 CYCLES.			NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.			○	—
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90~95 %, 96 h.			INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY.) 100 MΩ MIN. (AT DRY.)			○	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			○	—
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, 260 ± 5 °C FOR IMMERSION, DURATION 10 ± 1 S.			NO DEFORMATION OF CASE AND EXCESSIVE LOOSENESS OF THE TERMINALS.			○	—
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, 245 ± 2 °C FOR IMMERSION, DURATION 3 ± 1 S.			MIN. 95 % OF SOLDER IMMersed AREA SHALL BE COVERED NEW SOLDER COATING.			○	—
NOTE. 1 MEASUREMENT POINT OF CONTACT RESISTANCE									
									
REMARKS					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Unless otherwise specified, refer to JIS C 5402.					<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	
Note QT:Qualification Test AT:Assurance Test ○:Applicable Test									
HS HIROSE ELECTRIC CO., LTD.					SPECIFICATION SHEET			PART NO. DX20M-20S(50)	
CODE NO (OLD) CL			DRAWING NO. ELC4-041443-01			CODE NO. CL230-5013-8-50			1/1