

8462-01

Torque wrench DREMOMETER Z with quick-fitting change

8-1000 Nm / 70 lbf·in - 730 lbf·ft

Code
7704340ETIM
EC002132EAN
4002805846216UNSPSC
27-11-17-15Country of origin
GermanyeCI@ss
21-04-02-22Customs tariff number
82041100

Article description

- Classified according to DIN EN ISO 6789-2:2017 Type II Class A, incl. traceable test certificate, calibrated to a maximum permissible deviation of +/- 3 % and thus more precise than the +/- 4 % required by the standard
- Lightweight yet robust (as the housing is made of an aluminium alloy) and resilient, very workshop-friendly
- Depending on the application, access is possible from the front (e.g. open-end fitting) or side (e.g. reversible ratchet and socket).
- Force to be applied in the middle of the handgrip only - do not use an extension tube as otherwise, inaccuracies can evolve (except for model DXZ where the DREMOMETER has been calibrated and adjusted using the extension tube)
- Operation only with end fittings with standardised depth gauges, otherwise inaccuracies can arise. Keep the depth gauges on the certificate in mind. Only use original GEDORE accessories.
- Large drive cross-section transfers maximum torques
- Extremely low wear attributable to reduced forces in a lever mechanism
- Forged lever chain from our group own quality forge
- Maximum precision even when subjected to extreme continuous use
- Long life cycles and tool lives
- Easy operation - fast and safe torque tightening
- Easy adjustment thanks to attractive adjusting button secured against loss at the end of the handle
- With certificate acc. to DIN EN ISO 6789-2:2017, traceable via in-house DAkkS laboratory to national standards

Article information

Contents [Qty of pieces]	1	Precision +/-	+/- 3 %
Net weight [kg]	2 kg	Direction of tightening	Left and right
Total length [mm]	645 mm	Fixed setting	no
Total width [mm]	35 mm	Test certificate	DIN EN ISO 6789-2:2017
Total height [mm]	30 mm	Graduation	5
Material	Aluminum alloy	Head height 1 [mm]	30 mm
Depth gauge [metric]	32,0 mm	Width of head 1 [mm]	35,0 mm
Drive type/drive	Drive pin	Torque wrench type	CZ
Torque (min.) [Nm]	80 Nm	Distance between housing and centre of drive [mm].	16 mm
Torque (max.) [Nm]	400 Nm	Calibration length	567 mm
Torque (min.) [lbf·ft]	60 lbf·ft	Graduation [lbf·ft]	5 lbf·ft
Torque (max.) [lbf·ft]	300 lbf·ft	Lever length drive side [mm]	38 mm
Torque range (min./max.) [Nm]	80 Nm - 400 Nm	Lever length handle side [mm]	607 mm
Torque range (min./max.) [lbf·ft]	60 lbf·ft - 300 lbf·ft	Receptacle width [mm]	16 mm
Backup	Locking pin	Graduation [n·m]	5 Nm
Trigger mechanism	Short path triggering		