



Remote control switch 1 NO Central and group switching Contact for 230 V AC, 400V 16A Control 24 V AC

Model	
product brand name	SETRON
product designation	Remote control switch
latching relay design	Mechanical group switch
General technical data	
electrical endurance (operating cycles)	50 000
galvanic isolation between magnet coil and contact	Yes
switching voltage of the contacts at AC minimum	10 V
switching current at AC per contact minimum	100 mA
power loss [V·A] of magnet coil with pulse rated value	7 VA
Voltage	
type of voltage of the operating voltage	AC
continuous voltage fuse version	Yes
operating range factor control supply voltage rated value at AC at 50 Hz	
• initial value	0.8
• full-scale value	1.1
surge voltage resistance rated value	4 kV
supply voltage	250 V
Supply voltage	
supply voltage minimum	250 V
Protection class	
protection class IP	IP20, with connected conductors
Breaking Capacity	
switching capacity apparent power	
• for fluorescent lamp load with DUO circuit	700 VA
• for fluorescent lamp load with parallel compensation	300 VA
• for uncompensated fluorescent lamp load	400 VA
switching capacity current	
• at cos phi 0.6	16 A
• rated value	16 A
switching capacity active power with incandescent lamp load	2 000 W
Dissipation	
power loss [W]	
• at 16 A per contact rated value	1.2 W
• of magnet coil with pulse rated value	4.5 W
Control current	
type of voltage	
• of control voltage_1	AC

• of control voltage_2	AC
control voltage	
• _1 initial value	19 V
• _1 full-scale value	26 V
• _1 setpoint	24 V
• _2 initial value	19 V
• _2 full-scale value	26 V
• _2 setpoint	24 V
control voltage frequency	
• _1 initial value	50 Hz
• _1 full-scale value	50 Hz
• _2 initial value	50 Hz
• _2 full-scale value	50 Hz
operating range factor of control voltage_2	0.8

Product details

product component switch position indicator	Yes
number of NC contacts	0
number of NO contacts	1
number of CO contacts	0

Product function

product function direct operation	Yes
pulse duration minimum	50 ms

Number

number of terminals	8
----------------------------	---

Connections

connectable conductor cross-section for flexible conductor with core end processing	
• minimum	1 mm ²
• maximum	6 mm ²
connectable conductor cross-section for rigid conductor	
• minimum	1 mm ²
• maximum	6 mm ²
tightening torque with screw-type terminals	
• minimum	0.8 N·m
• maximum	1 N·m

Mechanical Design

height	90 mm
width	27 mm
width of opening of the contacts	1.2 mm
depth	76 mm
mounting height	90 mm
installation depth	70 mm
number of modular width units	1.5
fastening method	DIN rail
mounting position	any
required spacing for live parts	6 mm
net weight	144 g

Environmental conditions

ambient temperature during operation	
• minimum	-10 °C
• maximum	40 °C

Approvals Certificates


General Product Approval	Test Certificates	other
---------------------------------	--------------------------	--------------



[Miscellaneous](#)



other	Environment
--------------	--------------------

Further information**Information on the packaging**<https://support.industry.siemens.com/cs/ww/en/view/109813875>**Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT4151-2>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<https://support.industry.siemens.com/cs/ww/en/ps/5TT4151-2>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT4151-2**CAX-Online-Generator**<http://www.siemens.com/cax>**Tender specifications**<http://www.siemens.com/specifications>

last modified:

4/12/2025

