

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product form : Mixture
Product name : 007251 - SOUDURE NET FG
UFI : 2H2N-R00M-200H-M12Q
Product code : 007251
Type of product : Cleaner, Degreaser, Aerosol
Vaporizer : Aerosol

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.2.1. Relevant identified uses**

Industrial/Professional use spec : Industrial
For professional use only

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

ITW Spraytec
42, rue Gallieni
F-92600 Asnières sur Seine - France
T +33(0)1.40.80.32.32 - F +33(0)1.40.80.32.30
infofds@itwpc.com - www.jelt.fr

1.4. Emergency telephone number

Emergency number : FRANCE :+ 33 (0)1 45 42 59 59

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Newcastle Centre) Regional Drugs and Therapeutics Centre, Wolfson Unit	Claremont Place Newcastle-upon-Tyne NE1 4LP Newcastle	0344 892 0111	

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**


Aerosol, Category 1 H222;H229
Serious eye damage/eye irritation, Category 2 H319
Specific target organ toxicity — Single exposure, Category 3, Narcosis H336
Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements**Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP)



007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Signal word (CLP)	: Danger
Contains	: propan-2-ol; isopropyl alcohol; isopropanol
Hazard statements (CLP)	: H222 - Extremely flammable aerosol. H229 - Pressurised container: May burst if heated. H319 - Causes serious eye irritation. H336 - May cause drowsiness or dizziness.
Precautionary statements (CLP)	: P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P251 - Pressurized container: Do not pierce or burn, even after use. P271 - Use only outdoors or in a well-ventilated area. P337+P313 - If eye irritation persists: Get medical advice/attention. P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F. P102 - Keep out of reach of children.

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propan-2-ol; isopropyl alcohol; isopropanol	(CAS-No.) 67-63-0 (EC-No.) 200-661-7 (EC Index-No.) 603-117-00-0 (REACH-no) 01-2119457558-25	40 – 60	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
butane	(CAS-No.) 106-97-8 (EC-No.) 203-448-7	< 20	Flam. Gas 1A, H220 Press. Gas (Liq.), H280
1-methoxy-2-propanol; monopropylene glycol methyl ether	(CAS-No.) 107-98-2 (EC-No.) 203-539-1 (EC Index-No.) 603-064-00-3 (REACH-no) 01-2119457435-35	< 20	Flam. Liq. 3, H226 STOT SE 3, H336
Propane	(CAS-No.) 74-98-6 (EC-No.) 200-827-9 (REACH-no) 01-2119486944-21	< 10	Flam. Gas 1A, H220 Press. Gas (Liq.), H280
Dipropyleneglycol monomethylether	(CAS-No.) 34590-94-8 (EC-No.) 252-104-2 (REACH-no) 01-2119450011-60	< 10	Acute Tox. Not classified (Dermal)
Solution of ethyl sulfate N-alkyl coco dimethylethylammonium in butanol		< 1	Flam. Liq. 3, H226 Acute Tox. 4 (Oral), H302 Skin Corr. 1A, H314 STOT SE 3, H336 Aquatic Acute 1, H400

Product subject to CLP Article 1.1.3.7. The disclosure rules of the components is modified in this case.

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
----------------------------	---

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

First-aid measures after inhalation	: Cough. Remove person to fresh air and keep comfortable for breathing. Call a POISON CENTER/doctor if you feel unwell.
First-aid measures after skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Direct contact with the eyes is likely to be irritating. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation	: Shortness of breath. May cause drowsiness or dizziness.
Symptoms/effects after eye contact	: Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water haze. Carbon dioxide. Foam.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard	: Extremely flammable aerosol.
Explosion hazard	: Heat may build pressure, rupturing closed containers, spreading fire and increasing risk of burns and injuries.
Hazardous decomposition products in case of fire	: Thermal decomposition generates : Carbon monoxide. fume. Carbon dioxide.

5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. DO NOT fight fire when fire reaches explosives. Evacuate area.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: No open flames. No smoking. Isolate from fire, if possible, without unnecessary risk. Remove ignition sources. Use special care to avoid static electric charges.
------------------	---

6.1.1. For non-emergency personnel

Emergency procedures	: Evacuate unnecessary personnel.
----------------------	-----------------------------------

6.1.2. For emergency responders

Protective equipment	: Equip cleanup crew with proper protection. Avoid breathing dust/fume/gas/mist/vapours/spray.
Emergency procedures	: Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	: Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.
-------------------------	--

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed	: Hazardous waste due to potential risk of explosion. Do not pierce or burn, even after use.
Precautions for safe handling	: Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Do not spray on an open flame or other ignition source. Avoid breathing dust/fume/gas/mist/vapours/spray. Use only outdoors or in a well-ventilated area.
Hygiene measures	: Wash hands thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Proper grounding procedures to avoid static electricity should be followed.
Storage conditions	: Keep only in the original container in a cool, well ventilated place away from : Do not expose to temperatures exceeding 50 °C/ 122 °F. Keep in fireproof place. Keep container tightly closed.
Incompatible products	: Strong bases. Strong acids.
Incompatible materials	: Sources of ignition. Direct sunlight. Heat sources.
Storage temperature	: < 50 °C

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

propan-2-ol; isopropyl alcohol; isopropanol (67-63-0)

France - Occupational Exposure Limits

Local name	propane-2-ol, alcool isopropylique, isopropanol
VLE (mg/m³)	980 mg/m³
VLE (ppm)	400 ppm

Germany - Occupational Exposure Limits (TRGS 900)

TRGS 900 Local name	2-Propanol, Isopropylalkohol, Isopropanol
TRGS 900 Occupational exposure limit value (mg/m³)	500 mg/m³
TRGS 900 Occupational exposure limit value (ppm)	200 ppm
TRGS 900 Limitation of exposure peaks (mg/m³)	1000 mg/m³
TRGS 900 Limitation of exposure peaks (ppm)	400 ppm

1-methoxy-2-propanol; monopropylene glycol methyl ether (107-98-2)

France - Occupational Exposure Limits

Local name	1-Méthoxy-2-propanol
VME (mg/m³)	188 mg/m³
VME (ppm)	50 ppm
VLE (mg/m³)	375 mg/m³
VLE (ppm)	100 ppm

United Kingdom - Occupational Exposure Limits

Local name	1-Methoxypropan-2-ol
WEL TWA (mg/m³)	375 mg/m³
WEL TWA (ppm)	100 ppm

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

1-methoxy-2-propanol; monopropylene glycol methyl ether (107-98-2)

WEL STEL (mg/m ³)	560 mg/m ³
WEL STEL (ppm)	150 ppm
Remark (WEL)	Sk

butane (106-97-8)

France - Occupational Exposure Limits

Local name	n-Butane
VME (mg/m ³)	1900 mg/m ³
VME (ppm)	800 ppm

United Kingdom - Occupational Exposure Limits

Local name	Butane
WEL TWA (mg/m ³)	1450 mg/m ³
WEL TWA (ppm)	600 ppm
WEL STEL (mg/m ³)	1810 mg/m ³
WEL STEL (ppm)	750 ppm
Remark (WEL)	Carc, (only applies if Butane contains more than 0.1% of buta-1,3-diene)

Dipropyleneglycol monomethylether (34590-94-8)

France - Occupational Exposure Limits

Local name	(2-méthoxyméthylethoxy)-propanol
VME (mg/m ³)	308 mg/m ³
VME (ppm)	50 ppm

United Kingdom - Occupational Exposure Limits

Local name	(2-methoxymethylethoxy) propanol
WEL TWA (mg/m ³)	308 mg/m ³
WEL TWA (ppm)	50 ppm
Remark (WEL)	Sk

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Personal protective equipment:

Avoid all unnecessary exposure.

Materials for protective clothing:

Wear suitable protective clothing

Hand protection:

In case of repeated or prolonged contact wear gloves. Nitrile rubber gloves. The choice of appropriate gloves depends not only on the material, but also on other quality criteria that may vary from one manufacturer to another. As the product is a preparation made from several substances, glove material resistance may not be calculated in advance and must be tested before use. The exact penetration time of glove material is to be determined by the manufacturer of protective gloves and respected.

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Eye protection:

Safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

Personal protective equipment symbol(s):



Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Organic solvent.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: < 0 °C
Flash point	: < 0 °C
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Density	: 0,82 g/cm ³
Solubility	: soluble in most organic solvents.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

None under normal conditions.

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.2. Chemical stability

Stable under normal conditions. Heating may cause a fire or explosion. Extremely flammable aerosol.

10.3. Possibility of hazardous reactions

None under normal conditions.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Heat. Sparks. Open flame. Overheating.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

Thermal decomposition generates : fume. Carbon dioxide. Carbon monoxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

1-methoxy-2-propanol; monopropylene glycol methyl ether (107-98-2)

LD50 oral rat	5000 mg/kg
LD50 dermal rat	13500 mg/kg
LC50 inhalation rat (mg/l)	6000 µg/m³

Dipropylene glycol monomethylether (34590-94-8)

LD50 oral rat	> 4 mg/kg
LD50 dermal rabbit	9,5 mg/kg
LC50 inhalation rat (mg/l)	3,35 mg/l

Skin corrosion/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Causes serious eye irritation.
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: May cause drowsiness or dizziness.
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

007251 - SOUDURE NET FG

Vaporizer

Aerosol

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

12.2. Persistence and degradability

007251 - SOUDURE NET FG

Persistence and degradability

Not established.

12.3. Bioaccumulative potential

007251 - SOUDURE NET FG

Bioaccumulative potential

Not established.

1-methoxy-2-propanol; monopropylene glycol methyl ether (107-98-2)

Partition coefficient n-octanol/water (Log Pow)

0,37

Dipropylenglycol monomethylether (34590-94-8)

Partition coefficient n-octanol/water (Log Pow)

-0,35

Partition coefficient n-octanol/water (Log Kow)

0,004

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Container under pressure. Do not drill or burn even after use.

Additional information : Flammable vapours may accumulate in the container.

Ecology - waste materials : Avoid release to the environment.




SECTION 14: Transport information

In accordance with ADR / IATA / IMDG

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ADR	IMDG	IATA
14.1. UN number		
UN 1950	UN 1950	UN 1950
14.2. UN proper shipping name		
AEROSOLS	AEROSOLS	Aerosols, flammable
Transport document description		
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1
14.3. Transport hazard class(es)		
2.1	2.1	2.1
		
14.4. Packing group		
Not applicable	Not applicable	Not applicable
14.5. Environmental hazards		
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No
No supplementary information available		

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: 5F
Special provisions (ADR)	: 190, 327, 344, 625
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E0
Packing instructions (ADR)	: P207
Special packing provisions (ADR)	: PP87, RR6, L2
Mixed packing provisions (ADR)	: MP9
Transport category (ADR)	: 2
Special provisions for carriage - Packages (ADR)	: V14
Special provisions for carriage - Loading, unloading and handling (ADR)	: CV9, CV12
Special provisions for carriage - Operation (ADR)	: S2
Tunnel restriction code (ADR)	: D

Transport by sea

Special provisions (IMDG)	: 63, 190, 277, 327, 344, 381, 959
Packing instructions (IMDG)	: P207, LP200
Special packing provisions (IMDG)	: PP87, L2
EmS-No. (Fire)	: F-D
EmS-No. (Spillage)	: S-U
Stowage category (IMDG)	: None
Stowage and handling (IMDG)	: SW1, SW22
Segregation (IMDG)	: SG69

Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

CAO max net quantity (IATA) : 150kg
Special provisions (IATA) : A145, A167, A802
ERG code (IATA) : 10L

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

15.1.2. National regulations

France

Occupational diseases : RG 84 - Affections engendrées par les solvants organiques liquides à usage professionnel

Germany

Water hazard class (WGK) : WGK 1, Slightly hazardous to water (Classification according to AwSV, Annex 1)

Hazardous Incident Ordinance (12. BImSchV) : Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

Netherlands

SZW-lijst van kankerverwekkende stoffen : None of the components are listed

SZW-lijst van mutagene stoffen : None of the components are listed

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Borstvoeding

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Vruchtbaarheid

NIET-limitatieve lijst van voor de voortplanting : None of the components are listed

giftige stoffen – Ontwikkeling

Denmark

Class for fire hazard : Class I-1

Store unit : 1 liter

Classification remarks : F+ <Aerosol 1>; Emergency management guidelines for the storage of flammable liquids must be followed

Danish National Regulations : Young people below the age of 18 years are not allowed to use the product

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Acute Tox. Not classified (Dermal)	Acute toxicity (dermal) Not classified
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1

007251 - SOUDURE NET FG

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Gas 1A	Flammable gases, Category 1A
Flam. Liq. 2	Flammable liquids, Category 2
Flam. Liq. 3	Flammable liquids, Category 3
Press. Gas (Liq.)	Gases under pressure : Liquefied gas
Skin Corr. 1A	Skin corrosion/irritation, Category 1, Sub-Category 1A
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H220	Extremely flammable gas.
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H280	Contains gas under pressure; may explode if heated.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H400	Very toxic to aquatic life.

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.