









REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	ECN-24-284732	14SEP2024	F.F	M.S

- NOTE:
- MATERIAL: COPPER ALLOY
THICKNESS: 0.15MM
 - PLATING:
PRE TIN OVERALL
 - PART NUMBER ABBREVIATION AS MARK SHOWN
 - PACKAGED IN REEL INSIDE OF CARTON.

D



0.95...1.30 mm	0.22...0.35 mm ²	Pre_Tin	2	2834666-2
0.85...1.10 mm	0.13...0.17 mm ²	Pre_Tin	1	2834666-1
INSUL.DIA ISOØ	WIRE-SIZE DGB	FINISH	MARK	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FRANK FAN 23JAN2024	TE Connectivity		
DIMENSIONS: mm		CHK GEORGE FU 23JAN2024			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD MING SHI 23JAN2024	NAME DYNAMIC ULATRA TERMINAL		
0 PLC ± 1 PLC ±0.50 2 PLC ±0.25 3 PLC ±0.05 4 PLC ± ANGLES ±		PRODUCT SPEC -	SIZE A200779		
MATERIAL -		APPLICATION SPEC -	CAGE CODE C=C2834666		
FINISH -		WEIGHT -	DRAWING NO C2834666		
finish_spec_2		CUSTOMER DRAWING	RESTRICTED TO -		
		SCALE 7:1	SHEET 1 OF 1		
			REV A		

A

C

B