



Product data sheet

Power tools for trade & industry

Router

PRO GOF 20-12



Smooth routing with high working efficiency

The most important data

Part Number 0 601 627 271

Technical data

Technical data

Weight	6.3 kg
Packaging dimensions (width x length x height)	360 x 444 x 253 mm

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High routing efficiency thanks to 2000 W input power
- Stable cutting speed, thanks to the constant speed function
- Stepless and precise setup thanks to its after-lock micro depth adjustment mechanism
- Smoother operation with a longer contact surface of up to 355 mm thanks to the extendable guide plate



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

